

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0760107102

Status:

Active

Overview:

iPass Connector System

Description:

0.80mm Pitch iPass I/O Connector Shell, Vertical, Through Hole 3.18mm, 36 Circuits, Left Key

Documents:


Drawing (PDF)

Packaging Specification PK-76010-002 (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	I/O Connectors
Series	76010
Application	Wire-to-Board
Component Type	Shell Body
Material - Shield/Shell	Copper-Nickel-Zinc
Overview	iPass Connector System
Product Name	iPass
Type	N/A
UPC	822350748926
Physical	
Boot Color	N/A
Circuits (Loaded)	N/A
Circuits (maximum)	36
Circuits Detail	36
Durability (mating cycles max)	25
Gender	N/A
Keying to Mating Part	Yes
Lock to Mating Part	None
Material - Metal	Copper-Nickel-Zinc
Material - Plating Mating	N/A
Net Weight	1.738/g
Number of Rows	0
Orientation	Vertical
PC Tail Length	3.18mm
PCB Locator	No
PCB Retention	Yes
Packaging Type	Tray
Panel Mount	N/A
Pitch - Mating Interface	N/A
Polarized to Mating Part	N/A
Polarized to PCB	Yes
Surface Mount Compatible (SMC)	N/A
Temperature Range - Operating	-40° to +80°C
Termination Interface: Style	Through Hole
Waterproof / Dustproof	No
Wire Size AWG	N/A
Electrical	
Current - Maximum per Contact	N/A
Grounding to Panel	None
Shield Type	Full Shield
Shielded	Yes
Voltage - Maximum	N/A

Solder Process Data



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per - D(2020)9139-DC (19 Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

76010 Series

Mates With

79575 iPass Internal Cable, 74563 iPass Mini-SAS Internal Cable, 79576 iPass 36 Circuit-SATA Fanout Cable, 74573 iPass 36 Circuit RA-SATA Cable, 79536 iPass 36 Circuit SATA Cable, 74562 iPass 36 Circuit Right Angle

Use With

75577 0.80mm Pitch iPass I/O Connector

Duration at Max. Process Temperature (seconds)	015
Lead-freeProcess Capability	SMC&WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	260
Material Info	
Reference - Drawing Numbers	
Packaging Specification	PK-76010-002
Sales Drawing	SD-76010-002

This document was generated on 04/06/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[76010-7102](#)