

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0747522101](#)
Status: **Active**
Overview:
Description: SFP+-to-SFP+ Passive Cable Assembly, 10Gbps, 28 AWG Cable, Pull-to-Release Plunger Style Latch, 1.0m Length

Agency Certification	
UL	E72548
General	
Product Family	Cable Assemblies
Series	74752
Assembly Configuration	Dual Ended Connectors
Comments	Meets customer requirements for speeds up to 10 Gbps. Passive cables may require host pre-emphasis and equalization to reach at the longer lengths.
Connector to Connector	SFP+-to-SFP+
Overview	sfp_and_sfp_interconnect_solutions
Product Name	SFP Plus, SFP+
UPC	800756661223
Physical	
Cable Length	1.0m
Circuits (Loaded)	TWO DIFFERENTIAL PAIR
Gender	Male-Male
Lock to Mating Part	Yes
Material - Metal	Beryllium Copper, Zinc Alloy
Net Weight	94.088/g
Number of Rows	2
Packaging Type	Bag
Single Ended	No
Waterproof / Dustproof	Yes
Wire Insulation Diameter	N/A
Wire Size AWG	28
Wire/Cable Type	Twinax
Electrical	
Impedance	100Ω
Shield Type	Full Shield
Shielded	Yes
Voltage - Maximum	3.3V
Material Info	
Reference - Drawing Numbers	
Sales Drawing	747520001-000

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Contained Per -
D(2021)4569-DC (8
July 2021)
Diboron-trioxide
Bisphenol-A

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[74752](#) Series

Mates With

[74441](#) SFP+ Host Connector

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[74752-2101](#)