

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** [0747529001](#)  
**Status:** **Active**  
**Overview:** [SFP+ and SFP Interconnect Solutions](#)  
**Description:** SFP+-to-SFP+ Passive Cable Assembly, 10Gbps, 30 AWG Cable, Pull-to-Release Plunger Style Latch, 10.0m Length

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

UL E72548

**General**

Product Family Cable Assemblies  
Series [74752](#)  
Assembly Configuration Dual Ended Connectors  
Comments Meets customer requirements for speeds up to 10 Gbps. Passive cables may require host pre-emphasis and equalization to reach at the longer lengths.  
Connector to Connector SFP+-to-SFP+  
Overview [SFP+ and SFP Interconnect Solutions](#)  
Product Name SFP Plus, SFP+  
UPC 800756711591

**Physical**

Cable Length 10.0m  
Circuits (Loaded) TWO DIFFERENTIAL PAIR  
Gender Male-Male  
Lock to Mating Part Yes  
Material - Metal Beryllium Copper, Zinc Alloy  
Net Weight 313.000/g  
Number of Rows 2  
Packaging Type Bag  
Single Ended No  
Waterproof / Dustproof Yes  
Wire Insulation Diameter N/A  
Wire Size AWG 30  
Wire/Cable Type Twinax

**Electrical**

Impedance 100Ω  
Shield Type Full Shield  
Shielded Yes  
Voltage - Maximum 3.3V

**Material Info**



Series image - Reference only

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2021)4569-DC (8  
July 2021)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

|                 |               |
|-----------------|---------------|
| China ROHS      | Green Image   |
| ELV             | Not Relevant  |
| RoHS Phthalates | Not Contained |

**Search Parts in this Series**

[74752](#) Series

**Mates With**

[74441](#) SFP+ Host Connector

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[74752-9001](#)