

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0760155603

Status:

Active

Overview:

GbX I-Trac Backplane Connector System

Description:

GbX I-Trac Vertical Header Module, 1.85mm by 3.70mm Pitch, Right Guide, Left Open, 7 Rows, 6 Columns, 84 Circuits, Mating Pin Length 4.70mm, Lead-Free

Documents:

3D Model

Drawing (PDF)

Product Specification PS-75710-999-001 (PDF)

Packaging Specification PK-70873-802 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E29179
General	
Product Family	Backplane Connectors
Series	76015
Application	Backplane, Midplane, Orthogonal
Component Type	PCB Header
Overview	GbX I-Trac Backplane Connector System
Product Name	GbX I-Trac
UPC	822350872089
Physical	
Circuits (Loaded)	84
Circuits (maximum)	84
Color - Resin	Black
Durability (mating cycles max)	200
First Mate / Last Break	No
Flammability	94V-0
Guide to Mating Part	Yes
Keying to Mating Part	None
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	6.129/g
Number of Columns	6
Number of Pairs	4, Open Pin Field
Number of Rows	7
Orientation	Vertical
PC Tail Length	2.10mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Packaging Type	Tray
Pitch - Mating Interface	1.85mm, 3.70mm
Pitch - Termination Interface	1.00mm, 2.70mm
Plating min - Mating	0.762µm
Plating min - Termination	0.762µm
Polarized to PCB	No
Stackable	No
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	85°C
Termination Interface: Style	Through Hole - Compliant Pin

Electrical



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

Green Image

REACH SVHC

Not Contained Per - D(2020)4578-DC (25 June 2020)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

76015 Series

Mates With

76020 GbX I-Trac Right Angle Receptacle Module

Use With

78227 GbX I-Trac Vertical Power Receptacle. 75234 Backplane Free Standing Guide Pin

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Backplane Insertion	621005110
Tool for Signal	
Contact Insertion	

Current - Maximum per Contact	1.0A	Press-In Tool for	<u>622018608</u>
Data Rate	12.0 Gbps	Vertical Header 7-	
Shield Type	N/A	Row, 6-Column	
Shielded	No		
Voltage - Maximum	120V AC (RMS)/DC		
Solder Process Data			
Lead-freeProcess Capability	N/A		
Material Info			
Reference - Drawing Numbers			
Packaging Specification	PK-70873-802		
Product Specification	PS-75710-999-001		
Sales Drawing	SD-76015-004		

This document was generated on 09/04/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[76015-5603](#)