


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** [0752352764](#)  
**Status:** **Active**  
**Overview:** [GbX Backplane Connector System](#)  
**Description:** GbX 4 Pair Backplane Connector System, Left Guide Header, 56 Circuits, 7 Columns, Gold (Au) 0.76µm, Pin Length 4.55mm, Key Orientation F

**Documents:**  
[Drawing \(PDF\)](#) [Packaging Specification PK-70873-563 \(PDF\)](#)  
[Product Specification PS-75221-999-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

|                               |                                                                            |
|-------------------------------|----------------------------------------------------------------------------|
| <b>Agency Certification</b>   |                                                                            |
| UL                            | E29179                                                                     |
| <b>General</b>                |                                                                            |
| Product Family                | Backplane Connectors                                                       |
| Series                        | <a href="#">75235</a>                                                      |
| Application                   | Backplane                                                                  |
| Application Tooling Documents | TM-622022099                                                               |
| Comments                      | Left Guide Header, Keying Position F, Left Guide Header, Keying Position F |
| Component Type                | PCB Header                                                                 |
| Overview                      | <a href="#">GbX Backplane Connector System</a>                             |
| Product Name                  | GbX                                                                        |
| UPC                           | 822350176286                                                               |

|                                |                                               |
|--------------------------------|-----------------------------------------------|
| <b>Physical</b>                |                                               |
| Circuits (Loaded)              | 56                                            |
| Circuits (maximum)             | 56                                            |
| Color - Resin                  | Gray (Dark)                                   |
| Durability (mating cycles max) | 200                                           |
| First Mate / Last Break        | No                                            |
| Flammability                   | 94V-0                                         |
| Guide to Mating Part           | Yes                                           |
| Keying to Mating Part          | Yes                                           |
| Material - Metal               | High Performance Alloy (HPA), Stainless Steel |
| Material - Plating Mating      | Gold                                          |
| Material - Plating Termination | Tin-Lead                                      |
| Material - Resin               | High Temperature Thermoplastic                |
| Net Weight                     | 4.435/g                                       |
| Number of Columns              | 7                                             |
| Number of Pairs                | 4                                             |
| Number of Rows                 | 8                                             |
| Orientation                    | Vertical                                      |
| PC Tail Length                 | 2.20mm                                        |
| PCB Locator                    | No                                            |
| PCB Retention                  | Yes                                           |
| PCB Thickness - Recommended    | 1.60mm                                        |
| Packaging Type                 | Tray                                          |
| Pitch - Mating Interface       | 1.85mm                                        |
| Pitch - Termination Interface  | 1.85mm                                        |
| Plating min - Mating           | 0.762µm                                       |
| Plating min - Termination      | 0.762µm                                       |
| Polarized to PCB               | No                                            |
| Stackable                      | Yes                                           |
| Surface Mount Compatible (SMC) | Yes                                           |
| Temperature Range - Operating  | 105°C                                         |
| Termination Interface: Style   | Through Hole - Compliant Pin                  |



Series image - Reference only

|                                                                                                                                           |                   |
|-------------------------------------------------------------------------------------------------------------------------------------------|-------------------|
| <b>EU ELV</b><br><b>Not Relevant</b>                                                                                                      |                   |
| <b>EU RoHS</b><br><b>Not Reviewed</b><br><b>REACH SVHC</b><br>Not Reviewed<br><b>Halogen-Free</b><br><b>Status</b><br><b>Not Reviewed</b> | <b>China RoHS</b> |
| For more information, please visit <a href="#">Contact US</a>                                                                             |                   |
| China ROHS                                                                                                                                | Not Reviewed      |
| ELV                                                                                                                                       | Not Relevant      |
| RoHS Phthalates                                                                                                                           | Not Reviewed      |

**Search Parts in this Series**  
[75235](#) Series

**Mates With**  
[75220](#) GbX Daughtercard

**Application Tooling | FAQ**  
*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

|                                           |                           |
|-------------------------------------------|---------------------------|
| <b>Global</b>                             |                           |
| <b>Description</b>                        | <b>Product #</b>          |
| GbX Insertion Tool for 4-Pair by 7-Column | <a href="#">622022120</a> |

**Electrical**

|                               |                     |
|-------------------------------|---------------------|
| Current - Maximum per Contact | 1.0A                |
| Data Rate                     | 8.0 Gbps            |
| Real Signals (per 25mm)       | 108                 |
| Shield Type                   | Ground Plane Shield |
| Shielded                      | Yes                 |
| Voltage - Maximum             | 120V AC (RMS)/DC    |

**Solder Process Data**

|                             |     |
|-----------------------------|-----|
| Lead-freeProcess Capability | N/A |
|-----------------------------|-----|

**Material Info**

**Reference - Drawing Numbers**

|                         |                  |
|-------------------------|------------------|
| Packaging Specification | PK-70873-563     |
| Product Specification   | PS-75221-999-001 |
| Sales Drawing           | SD-75235-270     |

This document was generated on 09/14/2019

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

75235-2764