


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0761651323

Status: Active

Overview: Impact Backplane Connector and Cable Assembly System

Description: Impact 100 Ohm 3 Pair Vertical Backplane Header, Unguided, Dual Endwall, 6 Columns, 54 Circuits, Pin Length 4.50mm, Plated Through Hole Dimension 0.46mm, Lead-Free



Series image - Reference only

- Documents:**
- | | |
|--|---|
| 3D Model | Application Specification AS-76060-9999-001 (PDF) |
| Drawing (PDF) | Packaging Specification PK-70873-7700-001 (PDF) |
| 3D Model (PDF) | Symbol Footprint Data SYM-76165-1323-001 (PDF) |
| Product Specification PS-76060-999-001 (PDF) | RoHS Certificate of Compliance (PDF) |
| Application Specification AS-76060-990-001 (PDF) | |

Agency Certification	
UL	E29179
General	
Product Family	Backplane Connectors
Series	76165
Application	Conventional, Mezzanine
Application Tooling Documents	TM-622018799-001
Component Type	PCB Header
Overview	Impact Backplane Connector and Cable Assembly System
Product Name	Impact
UPC	884982362666
Physical	
Circuits (Loaded)	54
Circuits (maximum)	54
Color - Resin	Black
Durability (mating cycles max)	200
First Mate / Last Break	No
Flammability	94V-0
Guide to Mating Part	No
Keying to Mating Part	None
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	1.911/g
Number of Columns	6
Number of Pairs	3
Number of Rows	9
Orientation	Vertical
PC Tail Length	1.40mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.00mm
Packaging Type	Tray
Pitch - Mating Interface	1.90mm
Pitch - Termination Interface	1.90mm
Plating min - Mating	0.762µm
Polarized to PCB	No
Stackable	No
Temperature Range - Operating	-55° to +85°C

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

76165 Series

Mates With

76170 Impact 100 Ohm Daughtercard

Use With

75234 Backplane Free Standing Guide Pin

Termination Interface: Style	Through Hole - Compliant Pin
Electrical	
Current - Maximum per Contact	0.75A
Data Rate	25.0 Gbps
Impedance	100Ω
Shield Type	N/A
Shielded	No
Voltage - Maximum	30V AC (RMS)/DC
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Reference - Drawing Numbers	
Application Specification	AS-76060-990-001, AS-76060-9999-001
Packaging Specification	PK-70873-7700-001
Product Specification	PS-76060-999-001
Sales Drawing	SD-76165-001-001
Symbol/Footprint Data	SYM-76165-1323-001

This document was generated on 10/01/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[76165-1323](#)