

PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION

**Part Number:** [0752374163](#)  
**Status:** **Active**  
**Overview:** [GbX Backplane Connector System](#)  
**Description:** GbX 5 Pair Backplane Connector System, Right Guide Header, 100 Circuits, 10 Columns, Gold (Au) 0.76µm, Pin Length 3.55mm, Key Orientation F

**Documents:**

[3D Model](#) [Product Specification PS-75221-999-001 \(PDF\)](#)  
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**


UL E29179

**General**

Product Family Backplane Connectors  
Series [75237](#)  
Application Backplane  
Application Tooling Documents TM-622022099  
Comments Right Guide Header, Keying Position F, Right Guide Header, Keying Position F  
Component Type PCB Header  
Overview [GbX Backplane Connector System](#)  
Product Name GbX  
UPC 822350178075

**Physical**

Circuits (Loaded) 100  
Circuits (maximum) 100  
Color - Resin Gray (Dark)  
Durability (mating cycles max) 200  
First Mate / Last Break No  
Flammability 94V-0  
Guide to Mating Part Yes  
Keying to Mating Part Yes  
Material - Metal High Performance Alloy (HPA), Stainless Steel  
Material - Plating Mating Gold  
Material - Plating Termination Tin-Lead  
Material - Resin High Temperature Thermoplastic  
Net Weight 8.663/g  
Number of Columns 10  
Number of Pairs 5  
Number of Rows 10  
Orientation Vertical  
PC Tail Length 2.30mm  
PCB Locator No  
PCB Retention Yes  
PCB Thickness - Recommended 1.60mm  
Packaging Type Tray  
Pitch - Mating Interface 1.85mm  
Pitch - Termination Interface 1.85mm  
Plating min - Mating 0.762µm  
Plating min - Termination 0.762µm  
Polarized to PCB No  
Stackable Yes  
Surface Mount Compatible (SMC) Yes  
Temperature Range - Operating 105°C  
Termination Interface: Style Through Hole - Compliant Pin



Series image - Reference only

**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**China RoHS**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

|                 |              |
|-----------------|--------------|
| China ROHS      | Not Reviewed |
| ELV             | Not Relevant |
| RoHS Phthalates | Not Reviewed |

**Search Parts in this Series**

[75237](#) Series

**Mates With**

[75360](#) GbX Daughtercard

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

| Description                       | Product #                 |
|-----------------------------------|---------------------------|
| Insertion Tool, 5-Pair by 10-Wide | <a href="#">622022030</a> |
| Insertion Tool, 5-Pair by 20-Wide | <a href="#">622022040</a> |
| Single Pin Repair Tool            | <a href="#">622022090</a> |
| Shield Removal Tool               | <a href="#">622022100</a> |

**Electrical**

|                               |                     |
|-------------------------------|---------------------|
| Current - Maximum per Contact | 1.0A                |
| Data Rate                     | 8.0 Gbps            |
| Real Signals (per 25mm)       | 135                 |
| Shield Type                   | Ground Plane Shield |
| Shielded                      | Yes                 |
| Voltage - Maximum             | 120V AC (RMS)/DC    |

**Solder Process Data**

|                             |     |
|-----------------------------|-----|
| Lead-freeProcess Capability | N/A |
|-----------------------------|-----|

**Material Info**

**Reference - Drawing Numbers**

|                       |                  |
|-----------------------|------------------|
| Product Specification | PS-75221-999-001 |
| Sales Drawing         | SD-75237-410     |

This document was generated on 09/14/2019

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

75237-4163