

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0754330105

Status:

Active

Overview:

GbX Backplane Connector System

Description:

GbX 3 Pair Backplane Connector System, Open Header, 60 Circuits, 10 Columns, Gold (Au) 0.76µm, Pin Length 5.55mm

Documents:

3D Model

Packaging Specification PK-70873-576 (PDF)

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Product Specification PS-75221-999-001 (PDF)

Agency Certification

UL

E29179

General

Product Family

Series

Application

Application Tooling Documents

Comments

Component Type

Overview

Product Name

UPC

Backplane Connectors

75433

Backplane

TM-622022099

Open Header, Open Header

PCB Header

GbX Backplane Connector System

GbX

822350145466

Physical

Circuits (Loaded)

Circuits (maximum)

Color - Resin

Durability (mating cycles max)

First Mate / Last Break

Flammability

Guide to Mating Part

Keying to Mating Part

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Net Weight

Number of Columns

Number of Pairs

Number of Rows

Orientation

PC Tail Length

PCB Locator

PCB Retention

PCB Thickness - Recommended

Packaging Type

Pitch - Mating Interface

Pitch - Termination Interface

Plating min - Mating

Plating min - Termination

Polarized to PCB

Stackable

Surface Mount Compatible (SMC)

Temperature Range - Operating

Termination Interface: Style

60

60

Black

200

No

94V-0

No

None

High Performance Alloy (HPA)

Gold

Tin-Lead

High Temperature Thermoplastic

3.384/g

10

3

6

Vertical

2.20mm

No

Yes

1.60mm

Tube

1.85mm

1.85mm

0.762µm

0.762µm


No

Yes

Yes

105°C

Through Hole - Compliant Pin



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
ED/71/2019 (16 July
2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

75433 Series

Mates With

75370 GbX Daughtercards

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

Single Pin Repair Tool

622022090

Shield Removal Tool

622022100

3-Pair by 10-Wide Differential Insertion Tool

622022510

Electrical

Current - Maximum per Contact	1.0A
Data Rate	8.0 Gbps
Real Signals (per 25mm)	81
Shield Type	Ground Plane Shield
Shielded	Yes
Voltage - Maximum	120V AC (RMS)/DC

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-70873-576
Product Specification	PS-75221-999-001
Sales Drawing	SD-75433-010

This document was generated on 09/16/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[75433-0105](#)