


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0754332104](#)
Status: **Active**
Overview: [GbX Backplane Connector System](#)
Description: GbX 3 Pair Backplane Connector System, Left Guide Header, 60 Circuits, 10 Columns, Gold (Au) 0.76µm, Pin Length 4.55mm

Documents:
[3D Model](#) [Product Specification PS-75221-999-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [Packaging Specification PK-70873-572 \(PDF\)](#)
[3D Model \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification	
UL	E29179
General	
Product Family	Backplane Connectors
Series	75433
Application	Backplane
Application Tooling Documents	TM-622022099
Comments	Left Guide Header, No Keying Position, Left Guide Header, No Keying Position
Component Type	PCB Header
Overview	GbX Backplane Connector System
Product Name	GbX
UPC	822350116404

Physical	
Circuits (Loaded)	60
Circuits (maximum)	60
Color - Resin	Black
Durability (mating cycles max)	250
First Mate / Last Break	No
Flammability	94V-0
Guide to Mating Part	Yes
Keying to Mating Part	None
Material - Metal	High Performance Alloy (HPA), Stainless Steel
Material - Plating Mating	Gold
Material - Plating Termination	Tin-Lead
Material - Resin	High Temperature Thermoplastic
Net Weight	7.680/g
Number of Columns	10
Number of Pairs	3
Number of Rows	3
Orientation	Vertical
PC Tail Length	2.20mm
PCB Locator	No
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Tube
Pitch - Mating Interface	1.85mm
Pitch - Termination Interface	1.85mm
Plating min - Mating	0.762µm
Plating min - Termination	0.762µm
Polarized to PCB	Yes
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	105°C



Series image - Reference only

EU ELV Not Relevant	
EU RoHS Compliant REACH SVHC Not Contained Per - ED/71/2019 (16 July 2019) Halogen-Free Status Low-Halogen For more information, please visit Contact US	China RoHS
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[75433](#) Series

Mates With
[75370](#) GbX Daughtercards

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Single Pin Repair Tool	622022090
Shield Removal Tool	622022100
3-Pair by 10-Wide Differential Insertion Tool	622022510

Termination Interface: Style	Through Hole - Compliant Pin
Electrical	
Current - Maximum per Contact	1.0A
Data Rate	8.0 Gbps
Real Signals (per 25mm)	82
Shield Type	Ground Plane Shield
Shielded	Yes
Voltage - Maximum	120V AC (RMS)/DC
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Reference - Drawing Numbers	
Packaging Specification	PK-70873-572
Product Specification	PS-75221-999-001
Sales Drawing	SD-75433-210

This document was generated on 12/13/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

75433-2104