

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0781190910

Status:

Active

Overview:

Easy-On FFC FPC Connectors

Description:

0.50mm Pitch Easy-On FFC/FPC Connector, Surface Mount, Vertical, Non-ZIF, Standard Footprint, Tin Bismuth Plating, Short Terminal Type, Black, 9 Circuits



Documents:	
3D Model (PDF)	Product Specification 781190001-000 (PDF)
3D Model	Packaging Specification 781199200-200 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

General	
Product Family	FFC/FPC Connectors
Series	78119
Overview	Easy-On FFC FPC Connectors
Product Name	Easy-On
UPC	889056709118
Physical	
Actuator Type	Non-ZIF
Circuits (Loaded)	9
Circuits (maximum)	9
Color - Resin	Black
Contact Position	N/A
Durability (mating cycles max)	10
Mated Height	4.10mm
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin-Bismuth
Material - Plating Termination	Tin-Bismuth
Material - Resin	Liquid Crystal Polymer
Net Weight	107.687/mg
Number of Rows	1
Orientation	Vertical
PCB Locator	No
PCB Mounting	Surface Mount
PCB Retention	None
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	0.50mm
Pitch - Termination Interface	0.50mm
Plating min - Mating	1.000µm
Polarized to PCB	No
Stackable	No
Temperature Range - Operating	-40° to +85°C
Wire/Cable Type	FFC/FPC
Electrical	
Current - Maximum per Contact	0.5A
Voltage - Maximum	50V
Material Info	
Reference - Drawing Numbers	
Packaging Specification	781199200-200
Product Specification	781190001-000
Sales Drawing	781190001-000, 781191001-000

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

78119 Series

Mates With

Standard FFC/FPC Cables

This document was generated on 10/04/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[78119-0910](#)