

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0757057103

Status:

Active

Overview:

GbX I-Trac Backplane Connector System

Description:

GbX I-Trac Vertical Header Module, 1.85mm by 3.70mm Pitch, Left Guide, Right Endwall, 11 Rows, 10 Columns, 200 Circuits, Mating Pin Length 4.70mm

Documents:

3D Model

3D Model (PDF)

Drawing (PDF)

Product Specification PS-75710-999-001 (PDF)

Packaging Specification PK-70873-587 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E29179

General

Product Family

Series

Application

Component Type

Overview

Product Name

UPC

Backplane Connectors

75705

Backplane, Midplane, Orthogonal

PCB Header

GbX I-Trac Backplane Connector System

GbX I-Trac

800756720081

Physical

Circuits (Loaded)

Circuits (maximum)

Color - Resin

Durability (mating cycles max)

First Mate / Last Break

Flammability

Guide to Mating Part

Keying to Mating Part

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Net Weight

Number of Columns

Number of Pairs

Number of Rows

Orientation

PC Tail Length

PCB Locator

PCB Retention

PCB Thickness - Recommended

Packaging Type

Pitch - Mating Interface

Pitch - Termination Interface

Plating min - Mating

Plating min - Termination

Polarized to PCB

Stackable

Surface Mount Compatible (SMC)

Temperature Range - Operating

Termination Interface: Style

220

220

Black

200

No

94V-0

Yes

None

High Performance Alloy (HPA)

Gold

Tin

High Temperature Thermoplastic

11.273/g

10

6, Open Pin Field

11

Vertical

2.10mm

No

Yes

1.60mm

Tray

1.85mm, 3.70mm

1.00mm, 2.70mm

0.762µm

0.762µm

No


No

Yes

-55° to +80°C

Through Hole - Compliant Pin

Electrical



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -

D(2020)4578-DC (25

June 2020)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

75705 Series

Mates With

75710 GbX I-Trac Right Angle Receptacle Module

Use With

78232 GbX I-Trac Vertical Power Receptacle. 75234 Backplane Free Standing Guide Pin

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global Description	Product #
Backplane Insertion Tool for Signal Contact Insertion	621005110

Current - Maximum per Contact	1.0A	Press-In Tool for <u>622018603</u>
Data Rate	12.0 Gbps	Vertical Header 11-
Real Signals (per 25mm)	148	Row, 10-Column
Shield Type	N/A	
Shielded	No	
Voltage - Maximum	120V AC (RMS)/DC	
Solder Process Data		
Lead-freeProcess Capability	N/A	
Material Info		
Reference - Drawing Numbers		
Packaging Specification	PK-70873-587	
Product Specification	PS-75710-999-001	
Sales Drawing	SD-75705-002	

This document was generated on 08/24/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

75705-7103