

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0757057605

Status:

Active

Overview:

GbX I-Trac Backplane Connector System

Description:

GbX I-Trac Vertical Header Module, 1.85mm by 3.70mm Pitch, Left Guide, Right Endwall, 11 Rows, 6 Columns, 132 Circuits, Staggered Mating Pin Length 4.70mm & 5.70mm

Documents:

3D Model

Product Specification PS-75710-999-001 (PDF)

3D Model (PDF)

Packaging Specification PK-70873-587 (PDF)

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E29179

General

Product Family

Backplane Connectors

Series

75705

Application

Backplane, Midplane, Orthogonal

Component Type

PCB Header

Overview

GbX I-Trac Backplane Connector System

Product Name

GbX I-Trac

UPC

822350898430

Physical

Circuits (Loaded)

132

Circuits (maximum)

132

Color - Resin

Black

Durability (mating cycles max)

200

First Mate / Last Break

Yes

Flammability

94V-0

Guide to Mating Part

Yes

Keying to Mating Part

None

Material - Metal

High Performance Alloy (HPA)

Material - Plating Mating

Gold

Material - Plating Termination

Tin

Material - Resin

High Temperature Thermoplastic

Net Weight

8.639/g

Number of Columns

6

Number of Pairs

6, Open Pin Field

Number of Rows

11

Orientation

Vertical

PC Tail Length

2.10mm

PCB Locator

No

PCB Retention

Yes

PCB Thickness - Recommended

1.60mm

Packaging Type

Tray

Pitch - Mating Interface

1.85mm, 3.70mm

Pitch - Termination Interface

1.00mm, 2.70mm

Plating min - Mating

0.762µm

Plating min - Termination

0.762µm

Polarized to PCB

No

Stackable

No

Surface Mount Compatible (SMC)


Yes

Temperature Range - Operating

-55° to +80°C

Termination Interface: Style

Through Hole - Compliant Pin



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)4578-DC (25
June 2020)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

75705 Series

Mates With

75710 GbX I-Trac Right Angle Receptacle Module

Use With

78232 GbX I-Trac Vertical Power Receptacle. 75234 Backplane Free Standing Guide Pin

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

Backplane Insertion 621005110

Tool for Signal

Contact Insertion

Electrical

Current - Maximum per Contact	1.0A
Data Rate	12.0 Gbps
Real Signals (per 25mm)	148
Shield Type	N/A
Shielded	No
Voltage - Maximum	120V AC (RMS)/DC

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-70873-587
Product Specification	PS-75710-999-001
Sales Drawing	SD-75705-002

Press-In Tool for 622018602
Vertical Header 11-
Row, 6-Column

This document was generated on 08/24/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

75705-7605