

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0757575131

Status:

Active

Overview:

MX150 Sealed and Unsealed Connector System

Description:

MX150 Dual Row Header, Vertical, 6 Circuits, 2.5µm Tin (Sn) Plating, 16.09mm Mating Pin Length, 3.05mm PC Tail Length

Documents:

3D Model

Drawing (PDF)

3D Model (PDF)

Product Specification PS-75757-000-001 (PDF)

Packaging Specification PK-36518-340-001 (PDF)

Datasheet (PDF)

RoHS Certificate of Compliance (PDF)



Series image - Reference only

General

Product Family

Series

Application

Overview

Product Name

UPC

PCB Headers

75757

Power, Wire-to-Board

MX150 Sealed and Unsealed Connector System

MX150

800756794808

Physical

Breakaway

Circuits (Loaded)

Circuits (maximum)

Color - Resin

Durability (mating cycles max)

First Mate / Last Break

Glow-Wire Capable

Guide to Mating Part

Keying to Mating Part

Lock to Mating Part

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Net Weight

Number of Rows

Orientation

PC Tail Length

PCB Locator

PCB Retention

PCB Thickness - Recommended

Packaging Type

Pitch - Mating Interface

Pitch - Termination Interface

Plating min - Mating

Polarized to Mating Part

Polarized to PCB

Shrouded

Surface Mount Compatible (SMC)

Temperature Range - Operating

Termination Interface: Style

No

6

6

Black

25

No

No

No

None

None

Brass

Tin

Tin

High Temperature Thermoplastic

1.602/g

2

Vertical

3.05mm

No

None

1.57mm

Tube

3.50mm

3.50mm

2.540µm

No

No

No

Yes

-40° to +125°C

Through Hole

Electrical

Current - Maximum per Contact

Voltage - Maximum

17.0A

500V DC

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -

D(2021)4569-DC (8

July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit

Contact US

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

75757 Series

Mates With

33472 Dual Row MX150 Receptacles

Solder Process Data

Duration at Max. Process Temperature (seconds)	005
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	245

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-36518-340-001
Product Specification	PS-75757-000-001
Sales Drawing	SD-75757-002-001

This document was generated on 10/04/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[75757-5131](#)