

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0757575161

Status:

Active

Overview:

MX150™ Unshrouded Header

Description:

MX150 Dual Row Header, Vertical, 12 Circuits, 2.50µm Tin (Sn) Plating, 16.09mm Mating Pin Length, 3.05mm PC Tail Length

Documents:

- 3D Model

Product Specification PS-75757-000-001 (PDF)
- 3D Model (PDF)

Packaging Specification PK-36518-340 (PDF)
- Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

PCB Headers

Series

75757

Application

Power, Wire-to-Board

Overview

MX150™ Unshrouded Header

Product Name

MX150

UPC

800756810577

Physical

Breakaway

No

Circuits (Loaded)

12

Circuits (maximum)

12

Color - Resin

Black

Durability (mating cycles max)

25

First Mate / Last Break

No

Glow-Wire Capable

No

Guide to Mating Part

No

Keying to Mating Part

None

Lock to Mating Part

None

Material - Metal

Brass

Material - Plating Mating

Tin

Material - Plating Termination

Tin

Material - Resin

High Temperature Thermoplastic

Net Weight

3.693/g

Number of Rows

2

Orientation

Vertical

PC Tail Length

3.05mm

PCB Locator

No

PCB Retention

None

PCB Thickness - Recommended

1.57mm

Packaging Type

Tube

Pitch - Mating Interface

3.50mm

Pitch - Termination Interface

3.50mm

Plating min - Mating

2.540µm

Polarized to Mating Part

No

Polarized to PCB

No

Shrouded

No

Surface Mount Compatible (SMC)

Yes

Temperature Range - Operating

-40° to +125°C

Termination Interface: Style

Through Hole

Electrical

Current - Maximum per Contact

17.0A

Voltage - Maximum

500V DC

Solder Process Data



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

China RoHS

REACH SVHC

Not Contained Per -
ED/30/2017 (7 July
2017)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

75757 Series

Mates With

33472 Dual Row MX150 Receptacles

Duration at Max. Process Temperature (seconds)	005
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	245

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-36518-340
Product Specification	PS-75757-000-001
Sales Drawing	SD-75757-002-001

This document was generated on 04/01/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[75757-5161](#)