

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0785565051

Status:

Active

Overview:

DDR3 DIMM Sockets

Description:

1.00mm Pitch Aerodynamic DDR3 DIMM Socket, Low Profile, Vertical, Press-Fit, Blue Housing and Latches, 0.76µm Gold (Au Plating, 3.00mm PCB Thickness,240 Circuits, Lead-Free

Documents:

Drawing (PDF)

Product Specification PS-78556-001 (PDF)

Application Specification AS-78315-001-001 (PDF)

Application Specification AS-78556-001-001 (PDF)

Test Summary TS-78556-001-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification		
CSA		LR19980
UL		E29179
General		
Product Family		Memory Module Sockets
Series		78556
Component Type		Socket
Electrical Model		Yes
JEDEC Outline		SO-012
Overview		DDR3 DIMM Sockets
Product Name		DDR3 DIMM
UPC		884982636439

Physical		
Circuits (Loaded)		240
Circuits (maximum)		240
Durability (mating cycles max)		25
Entry Angle		Vertical
Flammability		94V-0
Housing Color		Blue
Keying to Mating Part		Yes
Latch Color		Blue
Material - Metal		Copper Alloy
Material - Plating Mating		Gold over Nickel
Material - Plating Termination		Tin
Material - Resin		Nylon
Net Weight		8.037/g
PC Tail Length		2.40mm, 2.60mm
PCB Locator		Yes
PCB Retention		Yes
PCB Thickness - Recommended		3.00mm
Packaging Type		Tray
Pitch - Mating Interface		1.00mm
Pitch - Termination Interface		1.00mm
Plating min - Mating		0.762µm
Plating min - Termination		0.381µm
Temperature Range - Operating		-55° to +85°C
Termination Interface: Style		Through Hole - Compliant Pin

Electrical		
Current - Maximum per Contact		1.0A
Voltage - Maximum		30V AC (RMS)/DC
Voltage Key		Center

Solder Process Data



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - ED/71/2019 (16 July 2019)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

78556 Series

Mates With

JEDEC Standard 1.27mm Modules

Lead-free	Process Capability	N/A
Material Info		
Reference - Drawing Numbers		
Application Specification	AS-78315-001-001, AS-78556-001-001	
Electrical Model Document	EE-78556-001, EE-78556-002, EE-78556-003, EE-78556-004	
Product Specification	PS-78556-001	
S-Parameter Model	SP-78556-001, SP-78556-002, SP-78556-003, SP-78556-004	
Signal Integrity Report	SI-78556-001	
Test Summary	TS-78556-001-001	

This document was generated on 09/18/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[78556-5051](#)