

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0787160014

Status:


Active

Overview:

Serial Attached SCSI (SAS) Connectors

Description:

1.27mm Signal Pitch, 0.80mm SCSI Pitch, 1.27mm Power Pitch SAS-3 Receptacle, Vertical, Hybrid, with Blade, 2.34mm PCB Thickness, 29 Circuits, with Cap, Embossed Tape on Reel, Lead-Free



Documents:	
3D Model	Application Specification AS-78716-001-001 (PDF)
Drawing (PDF)	Packaging Specification PK-78716-002-001 (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-78716-001-001 (PDF)	

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	I/O Connectors
Series	78716
Application	Board-to-Board
Component Type	Receptacle
Electrical Model	Yes
Overview	Serial Attached SCSI (SAS) Connectors
Product Name	SAS 12G, SAS-3
Type	N/A
UPC	887191201962
Physical	
Circuits (Loaded)	29
Circuits Detail	Signal 14, Power 15
Color - Resin	Black
Durability (mating cycles max)	500
Flammability	94V-0
Gender	Female
Keying to Mating Part	Yes
Lock to Mating Part	None
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	1.861/g
Number of Rows	2
Orientation	Vertical
PC Tail Length	2.36mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	2.34mm
Packaging Type	Embossed Tape on Reel
Panel Mount	No
Pitch - Mating Interface	0.80mm, 1.27mm
Pitch - Termination Interface	0.80mm, 1.27mm
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Surface Mount Compatible (SMC)	Yes

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

78716 Series

Mates With

SAS / SATA plug

Temperature Range - Operating	0° to +55°C
Termination Interface: Style	Surface Mount and Through Hole
Waterproof / Dustproof	No
Electrical	
Current - Maximum per Contact	1.5A
Voltage - Maximum	30V
Solder Process Data	
Duration at Max. Process Temperature (seconds)	010
Lead-freeProcess Capability	REFLOW
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	260
Material Info	
Reference - Drawing Numbers	
Application Specification	AS-78716-001-001
Electrical Model Document	EE-78716-001-001
Packaging Specification	PK-78716-002-001
Product Specification	PS-78716-001-001
S-Parameter Model	SP-78716-001-001
Sales Drawing	SD-78716-001-001

This document was generated on 10/04/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[78716-0014](#)