

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0787280002

Status:


Active

Overview:

Serial Attached SCSI (SAS) Connectors

Description:

1.27mm Signal Pitch, 0.80mm SCSI Pitch, 1.27mm Power Pitch SAS-3 Receptacle, Vertical, Surface Mount, with Side Solder Tabs, 1.60mm PCB Thickness, 29 Circuits, with Cap, 45.75mm Length, 5.50mm Width, Embossed Tape on Reel, Lead-Free



- Documents:
- 3D Model

Packaging Specification PK-78728-003-001 (PDF)
- 3D Model (PDF)

Test Summary TS-78728-001-001 (PDF)
- Drawing (PDF)

Test Summary TS-78728-002-001 (PDF)
- Product Specification PS-78728-001-001 (PDF)

RoHS Certificate of Compliance (PDF)
- Application Specification AS-78728-001-001 (PDF)

| Agency Certification           |                                       |
|--------------------------------|---------------------------------------|
| CSA                            | LR19980                               |
| UL                             | E29179                                |
| General                        |                                       |
| Product Family                 | I/O Connectors                        |
| Series                         | 78728                                 |
| Application                    | Board-to-Board                        |
| Component Type                 | Receptacle                            |
| Electrical Model               | Yes                                   |
| Overview                       | Serial Attached SCSI (SAS) Connectors |
| Product Name                   | SAS 12G, SAS-3                        |
| Type                           | N/A                                   |
| UPC                            | 887191309255                          |
| Physical                       |                                       |
| Circuits (Loaded)              | 29                                    |
| Circuits Detail                | Signal 14, Power 15                   |
| Color - Resin                  | Black                                 |
| Durability (mating cycles max) | 500                                   |
| Flammability                   | 94V-0                                 |
| Gender                         | Female                                |
| Keying to Mating Part          | Yes                                   |
| Lock to Mating Part            | None                                  |
| Material - Metal               | Copper Alloy                          |
| Material - Plating Mating      | Gold                                  |
| Material - Plating Termination | Tin                                   |
| Material - Resin               | High Temperature Thermoplastic        |
| Net Weight                     | 1.544/g                               |
| Number of Rows                 | 2                                     |
| Orientation                    | Vertical                              |
| PCB Locator                    | Yes                                   |
| PCB Retention                  | Yes                                   |
| PCB Thickness - Recommended    | 1.60mm                                |
| Packaging Type                 | Embossed Tape on Reel                 |
| Panel Mount                    | No                                    |
| Pitch - Mating Interface       | 0.80mm, 1.27mm                        |
| Pitch - Termination Interface  | 0.80mm, 1.27mm                        |
| Plating min - Mating           | 0.762µm                               |
| Plating min - Termination      | 2.540µm                               |
| Polarized to Mating Part       | Yes                                   |
| Polarized to PCB               | Yes                                   |
| Surface Mount Compatible (SMC) | Yes                                   |

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2021)4569-DC (8 July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

78728 Series

Mates With

SAS / SATA plug

|                                                |                                    |
|------------------------------------------------|------------------------------------|
| Temperature Range - Operating                  | 0° to +55°C                        |
| Termination Interface: Style                   | Surface Mount                      |
| Waterproof / Dustproof                         | No                                 |
| <b>Electrical</b>                              |                                    |
| Current - Maximum per Contact                  | 1.5A                               |
| Voltage - Maximum                              | 30V                                |
| <b>Solder Process Data</b>                     |                                    |
| Duration at Max. Process Temperature (seconds) | 010                                |
| Lead-freeProcess Capability                    | REFLOW                             |
| Max. Cycles at Max. Process Temperature        | 001                                |
| Process Temperature max. C                     | 260                                |
| <b>Material Info</b>                           |                                    |
| <b>Reference - Drawing Numbers</b>             |                                    |
| Application Specification                      | AS-78728-001-001                   |
| Electrical Model Document                      | EE-78728-001-001                   |
| Packaging Specification                        | PK-78728-003-001                   |
| Product Specification                          | PS-78728-001-001                   |
| S-Parameter Model                              | SP-78728-001-001                   |
| Sales Drawing                                  | SD-78728-001-000                   |
| Signal Integrity Report                        | SI-78728-001-001                   |
| Test Summary                                   | TS-78728-001-001, TS-78728-002-001 |

This document was generated on 10/04/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[78728-0002](#)