

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0757830209

Status:


Active

Overview:

iPass Connector System

Description:

iPass I/O Surface Mount Receptacle, 0.80mm Pitch, Right-Angle, Internal Assembly with Shell, 50 Circuit, 0.38µm Gold (Au), Retention-Fit Shell Option, Tail Length 1.96mm, Dual Key



Series image - Reference only

- Documents:
- [3D Model](#)

[Drawing \(PDF\)](#)

[3D Model \(PDF\)](#)

[Product Specification PS-75783-001-001 \(PDF\)](#)
- [Application Specification AS-75783-001 \(PDF\)](#)

[Packaging Specification PK-75783-002 \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

|                                |                                                  |
|--------------------------------|--------------------------------------------------|
| Agency Certification           |                                                  |
| CSA                            | LR19980                                          |
| UL                             | E29179                                           |
| General                        |                                                  |
| Product Family                 | I/O Connectors                                   |
| Series                         | 75783                                            |
| Application                    | Wire-to-Board                                    |
| Comments                       | Positive or passive latching cable available     |
| Component Type                 | Receptacle                                       |
| Electrical Model               | Yes                                              |
| Overview                       | iPass Connector System                           |
| Product Name                   | iPass, Mini Multi-Lane, PCI Express              |
| Type                           | N/A                                              |
| UPC                            | 822350092432                                     |
| Physical                       |                                                  |
| Circuits (Loaded)              | 50                                               |
| Circuits (maximum)             | 50                                               |
| Color - Resin                  | Black                                            |
| Durability (mating cycles max) | 50                                               |
| Flammability                   | 94V-0                                            |
| Gender                         | Female                                           |
| Keying to Mating Part          | Yes                                              |
| Lock to Mating Part            | None                                             |
| Material - Metal               | Copper-Nickel-Zinc, High Performance Alloy (HPA) |
| Material - Plating Mating      | Gold                                             |
| Material - Plating Termination | Tin                                              |
| Material - Resin               | High Temperature Thermoplastic                   |
| Net Weight                     | 3.810/g                                          |
| Number of Rows                 | 2                                                |
| Orientation                    | Right Angle                                      |
| PC Tail Length                 | 1.96mm                                           |
| PCB Locator                    | Yes                                              |
| PCB Retention                  | Yes                                              |
| PCB Thickness - Recommended    | 1.57mm                                           |
| Packaging Type                 | Embossed Tape on Reel                            |
| Panel Mount                    | No                                               |
| Pitch - Mating Interface       | 0.80mm                                           |
| Pitch - Termination Interface  | 0.80mm                                           |
| Plating min - Mating           | 0.381µm                                          |
| Plating min - Termination      | 2.540µm                                          |
| Polarized to Mating Part       | Yes                                              |
| Ports                          | 1                                                |

|                                                               |               |
|---------------------------------------------------------------|---------------|
| EU ELV                                                        |               |
| Not Relevant                                                  |               |
| EU RoHS                                                       | China RoHS    |
| Compliant                                                     |               |
| REACH SVHC                                                    |               |
| Not Contained Per - D(2020)9139-DC (19 Jan 2021)              |               |
| Halogen-Free                                                  |               |
| Status                                                        |               |
| Low-Halogen                                                   |               |
| For more information, please visit <a href="#">Contact US</a> |               |
| China ROHS                                                    | Green Image   |
| ELV                                                           | Not Relevant  |
| RoHS Phthalates                                               | Not Contained |

Search Parts in this Series

75783 Series

Use With

iPass Cable Assemblies, [79575](#) , [79576](#) , [74562](#) , [74563](#) , [79536](#) , [74573](#) ,

|                                    |                  |
|------------------------------------|------------------|
| Surface Mount Compatible (SMC)     | Yes              |
| Temperature Range - Operating      | -40° to +80°C    |
| Termination Interface: Style       | Surface Mount    |
| Waterproof / Dustproof             | No               |
| Wire Insulation Diameter           | N/A              |
| Wire Size AWG                      | N/A              |
| <b>Electrical</b>                  |                  |
| Current - Maximum per Contact      | 0.5A             |
| Grounding to Panel                 | None             |
| Voltage - Maximum                  | 30V AC (RMS)/DC  |
| <b>Solder Process Data</b>         |                  |
| Lead-freeProcess Capability        | REFLOW           |
| Process Temperature max. C         | 260              |
| <b>Material Info</b>               |                  |
| <b>Reference - Drawing Numbers</b> |                  |
| Application Specification          | AS-75783-001     |
| Electrical Model Document          | EE-75586-001     |
| Packaging Specification            | PK-75783-002     |
| Product Specification              | PS-75783-001-001 |
| S-Parameter Model                  | SP-75586-001     |
| Sales Drawing                      | SD-75783-001-001 |

This document was generated on 04/12/2021

PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[75783-0209](#)