

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0788320006](#)
Status: **Active**
Overview: [Serial Attached SCSI \(SAS\) Connectors](#)
Description: 0.80mm Signal Pitch, 1.27mm Power Pitch Micro SAS-3 Receptacle, Vertical, Surface Mount, 0.76µm Selective Gold (Au) Plating, 25 Circuits, for 1.00mm PCB Thickness, Halogen free, Lead-Free

Documents:
[3D Model](#) [Application Specification AS-78832-001-001 \(PDF\)](#)
[3D Model \(PDF\)](#) [Packaging Specification PK-78832-001-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-78832-001-001 \(PDF\)](#)

Agency Certification


CSA	LR19980
UL	E29179

General

Product Family	I/O Connectors
Series	78832
Application	Board-to-Board
Component Type	Receptacle
Electrical Model	Yes
Overview	Serial Attached SCSI (SAS) Connectors
Product Name	Micro SAS 12G, Micro SAS-3
Type	N/A
UPC	887191534718

Physical

Boot Color	N/A
Circuits (Loaded)	25
Circuits (maximum)	25
Circuits Detail	Signal 14, Power 9, Sideband 2
Color - Resin	Black
Durability (mating cycles max)	500
Flammability	94V-0
Gender	Female
Keying to Mating Part	Yes
Lock to Mating Part	None
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	0.813/g
Number of Rows	2
Orientation	Vertical
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.00mm
Packaging Type	Embossed Tape on Reel
Panel Mount	No
Pitch - Mating Interface	0.80mm, 1.27mm
Pitch - Termination Interface	0.80mm, 1.27mm
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[78832](#) Series

Temperature Range - Operating	0° to +55°C
Termination Interface: Style	Surface Mount
Waterproof / Dustproof	No
Electrical	
Current - Maximum per Contact	1.5A
Voltage - Maximum	30V
Solder Process Data	
Duration at Max. Process Temperature (seconds)	010
Lead-freeProcess Capability	REFLOW
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	260
Material Info	
Reference - Drawing Numbers	
Application Specification	AS-78832-001-001
Electrical Model Document	EE-78832-002-001
Packaging Specification	PK-78832-001-001
Product Specification	PS-78832-001-001
S-Parameter Model	SP-78832-002-001
Sales Drawing	SD-78832-001-001, SD-78832A-001-001

This document was generated on 10/05/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[78832-0006](#)