

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0850033108

Status:

Active

Overview:

DIN 41612

Description:

2.54mm Pitch DIN 41612 C/2 Style Male Header, Right-Angle, Through Hole, 0.80µm Selective Gold (Au) Plating, 48 Circuits, without Mounting Clips, No Flux Proof

Documents:

Drawing (PDF)

Product Specification PS-85003-0001-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification


CSA	LR19980
UL	E29179

General

Product Family	Backplane Connectors
Series	85003
Application	Backplane
Comments	No Mounting Clips. No Flux Proof. 4.20mm Last-Mate-First-Break Contacts. 5.40mm First-Mate-Last-Break Contacts. 4.80mm Normal Contacts, No Mounting Clips. No Flux Proof. 4.20mm Last-Mate-First-Break Contacts. 5.40mm First-Mate-Last-Break Contacts. 4.80mm Normal Contacts
Component Type	PCB Header
Overview	DIN 41612
Product Name	IEC 603-2/DIN 41612
Style	C/2
UPC	800753874022

Physical

Circuits (Loaded)	48
Circuits (maximum)	48
Circuits Detail	Standard Contacts at: A:a2-a8,a10-a15; B:b1-b16; C:c1-c4,c6-c16. Last-Mate-First-Break Contacts at: D:a16. First-Mate-Last-Break Contacts at:X:c5; Z:a1,a9
Color - Resin	Gray
Durability (mating cycles max)	400
First Mate / Last Break	Yes
Flammability	94V-0
Guide to Mating Part	No
Keying to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Polyester
Number of Columns	16
Number of Pairs	Open Pin Field
Number of Rows	3
Orientation	Right Angle
PC Tail Length	3.00mm
PCB Locator	No
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Carton
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
85003 Series

Plating min - Mating	0.813μm
Plating min - Termination	2.540μm
Polarized to PCB	Yes
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-55° to +125°C
Termination Interface: Style	Through Hole
Electrical	
Current - Maximum per Contact	1.0A
Data Rate	622.0 Mbps
Voltage - Maximum	250V AC (RMS)
Material Info	
Reference - Drawing Numbers	
Product Specification	PS-85003-0001-001
Sales Drawing	SD-85003-3108

This document was generated on 04/02/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[85003-3108](#)