

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0850037031](#)
Status: **Active**
Overview: [DIN 41612](#)
Description: 2.54mm Pitch DIN 41612 C Style Male Header, Right Angle, Through Hole, 0.60µm Selective Gold (Au) Plating, 23 Circuits, with Mounting Clips, No Flux Proof, High Temperature version

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-85003-0001-001 \(PDF\)](#)

Agency Certification


CSA LR19980
UL E29179

General

Product Family Backplane Connectors
Series [85003](#)
Application Backplane
Comments With Mounting Clips. No Flux Proof
Component Type PCB Header
Overview [DIN 41612](#)
Product Name IEC 603-2/DIN 41612
Style C
UPC 800753239425

Physical

Circuits (Loaded) 23
Circuits (maximum) 96
Circuits Detail Standard Contacts at:
A:a9,a11,a15,a17,a19,a21,a22,a31,a32; B:b4-b11,b20,b23,b32; C:c9,c31,c32
Color - Resin Natural
Durability (mating cycles max) 400
First Mate / Last Break No
Flammability 94V-0
Guide to Mating Part No
Keying to Mating Part Yes
Material - Metal Brass
Material - Plating Mating Gold
Material - Plating Termination Tin
Material - Resin High Temperature Thermoplastic
Number of Columns 16
Number of Pairs Open Pin Field
Number of Rows 3
Orientation Right Angle
PC Tail Length 3.00mm
PCB Locator No
PCB Retention Yes
PCB Thickness - Recommended 1.60mm
Packaging Type Carton
Pitch - Mating Interface 2.54mm
Pitch - Termination Interface 2.54mm
Plating min - Mating 0.610µm
Plating min - Termination 2.540µm
Polarized to PCB Yes
Stackable No



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[85003](#) Series

Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-55°C to +125°C
Termination Interface: Style	Through Hole
Electrical	
Current - Maximum per Contact	2.5A
Data Rate	622.0 Mbps
Voltage - Maximum	250V AC (RMS)
Material Info	
Reference - Drawing Numbers	
Product Specification	PS-85003-0001-001
Sales Drawing	SD-85003-7031

This document was generated on 10/31/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[85003-7031](#)