

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0850150311

Status:

Active

Overview:


DIN 41612

Description:

2.54mm Pitch DIN 41612 Header, Through Hole, Vertical, Press-fit Style R, 0.60µm Gold (Au), 128 Circuit, Lead-Free

Documents:	
3D Model	Product Specification PS-85013-0002 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	Backplane Connectors
Series	85015
Application	Backplane
Comments	R at Style Represents Vertical Male DIN Connectors, R at Style Represents Vertical Male DIN Connectors
Component Type	PCB Header
Overview	DIN 41612
Product Name	IEC 603-2/DIN 41612
Style	R
UPC	800753197558
Physical	
Circuits (Loaded)	128
Circuits (maximum)	128
Circuits Detail	Rows A, B, C, & D
Color - Resin	Gray
Durability (mating cycles max)	400
First Mate / Last Break	No
Flammability	94V-0
Guide to Mating Part	No
Keying to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Polyester
Net Weight	17.714/g
Number of Columns	32
Number of Pairs	Open Pin Field
Number of Rows	4
Orientation	Vertical
PC Tail Length	5.80mm
PCB Locator	No
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm, 4.00mm
Packaging Type	Carton
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Plating min - Mating	0.610µm
Plating min - Termination	0.406µm
Polarized to PCB	Yes
Stackable	No
Surface Mount Compatible (SMC)	No



EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - ED/71/2019 (16 July 2019)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

85015 Series

Mates With

85042 DIN 41612 Receptacle. 85052 DIN 41612 Header

Use With

850891081 Press-in Tool

Temperature Range - Operating	-55° to +125°C
Termination Interface: Style	Through Hole - Compliant Pin
Electrical	
Current - Maximum per Contact	1.0A
Data Rate	622.0 Mbps
Voltage - Maximum	250V AC (RMS)
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Reference - Drawing Numbers	
Product Specification	PS-85013-0002
Sales Drawing	SDA-85015-0311

This document was generated on 09/18/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[85015-0311](#)