

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0850480969](#)
Status: **Active**
Overview: [DIN 41612](#)
Description: 2.54mm Pitch DIN 41612/IEC 603-2 Mixed Layout Connector, Through Hole, Vertical, Female Style M, 32 Circuits, Lead-Free

Documents:

[3D Model](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Drawing \(PDF\)](#)

Agency Certification

CSA LR19980
UL E29179

General


Product Family Backplane Connectors
Series [85048](#)
Application Backplane
Comments Mixed Layout, Mixed Layout
Component Type PCB Receptacle
Overview [DIN 41612](#)
Product Name IEC 603-2/DIN 41612
Style M
UPC 800753857551

Physical

Circuits (Loaded) 32
Circuits (maximum) 32
Circuits Detail Rows A, B, & C
Durability (mating cycles max) 400
First Mate / Last Break No
Flammability 94V-0
Guide to Mating Part No
Keying to Mating Part Yes
Material - Metal Copper Alloy
Material - Plating Mating Gold
Material - Plating Termination Tin
Net Weight 8.825/g
Number of Columns 8
Number of Pairs Open Pin Field
Number of Rows 3
Orientation Vertical
PC Tail Length 2.90mm
PCB Locator No
PCB Retention Yes
Packaging Type Carton
Pitch - Mating Interface 2.54mm
Pitch - Termination Interface 2.54mm
Plating min - Mating 0.610µm
Polarized to PCB Yes
Stackable No
Surface Mount Compatible (SMC) No
Temperature Range - Operating -55° to +125°C
Termination Interface: Style Through Hole

Electrical

Current - Maximum per Contact 1.0A



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/71/2019 (16 July
2019)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[85048](#) Series

Mates With

DIN 41612/EIC 603-2 Mixed Layout
Connector [85009](#) , [85017](#)

Use With

[85022](#)

Data Rate	622.0 Mbps
Real Signals (per 25mm)	30
Voltage - Maximum	250V AC (RMS)
Solder Process Data	
Duration at Max. Process Temperature (seconds)	010
Lead-freeProcess Capability	WAVE
Process Temperature max. C	260
Material Info	
Reference - Drawing Numbers	
Sales Drawing	SD-85048-0004, SD-85048-0969

This document was generated on 09/17/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[85048-0969](#)