

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0758580104

Status:

Active

Overview:

GbX Backplane Connector System

Description:

GbX 3 Pair L-Series Backplane Signal Header, Open Header, 80 Circuits, 10 Columns, Gold (Au) 0.76µm, Pin Length 4.55mm, Lead-Free

Documents:

3D Model

3D Model (PDF)

Drawing (PDF)

Product Specification PS-75221-999-001 (PDF)

Packaging Specification PK-70873-576 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E29179

General

Product Family

Series

Application

Application Tooling Documents

Comments

Component Type

Overview

Product Name

UPC

Backplane Connectors

75858

Backplane

TM-622022099

Open Header, Open Header

PCB Header

GbX Backplane Connector System

GbX

822350423106

Physical

Circuits (Loaded)

Circuits (maximum)

Color - Resin

Durability (mating cycles max)

First Mate / Last Break

Flammability

Guide to Mating Part

Keying to Mating Part

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Net Weight

Number of Columns

Number of Pairs

Number of Rows

Orientation

PC Tail Length

PCB Locator

PCB Retention

PCB Thickness - Recommended

Packaging Type

Pitch - Mating Interface

Pitch - Termination Interface

Plating min - Mating

Plating min - Termination

Polarized to PCB

Stackable

Surface Mount Compatible (SMC)

Temperature Range - Operating

Termination Interface: Style

80

80

Black

200

No

94V-0

No

None

High Performance Alloy (HPA)

Gold

Tin

High Temperature Thermoplastic

3.002/g

10

4

8

Vertical

2.30mm

No

Yes

1.60mm

Tray

1.85mm

1.85mm

0.762µm

0.762µm


No

Yes

Yes

105°C

Through Hole - Compliant Pin



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per - ED/71/2019 (16 July 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

75858 Series

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
GbX 3-Pair by 25-Wide Differential Insertion Tool	622022550

Electrical

Current - Maximum per Contact	1.0A
Data Rate	8.0 Gbps
Shielded	No
Voltage - Maximum	120V AC (RMS)/DC

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-70873-576
Product Specification	PS-75221-999-001
Sales Drawing	SD-75858-010

This document was generated on 12/18/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[75858-0104](#)