

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0758614204](#)
Status: **Active**
Overview: [GbX Backplane Connector System](#)
Description: GbX 2 Pair L-Series Backplane Connector System, Right Guide Header, 125 Circuits, Gold (Au) 0.76µm, Pin Length 4.55mm

Documents:

[3D Model](#) [Packaging Specification PK-70873-5058 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General


Product Family Backplane Connectors
Series [75861](#)
Application Backplane
Application Tooling Documents TM-622022099
Comments Left Guide Header, No Keying Position, Left Guide Header, No Keying Position
Component Type PCB Header
Overview [GbX Backplane Connector System](#)
Product Name GbX
UPC 800756809465

Physical

Circuits (Loaded) 125
Circuits (maximum) 125
Color - Resin Gray (Dark)
Durability (mating cycles max) 200
First Mate / Last Break No
Guide to Mating Part Yes
Keying to Mating Part None
Material - Metal High Performance Alloy (HPA), Stainless Steel
Material - Plating Mating Gold
Material - Plating Termination Tin-Lead
Material - Resin High Temperature Thermoplastic
Net Weight 8.785/g
Number of Columns 25
Number of Pairs 2
Number of Rows 5
Orientation Vertical
PC Tail Length 2.20mm
PCB Locator No
PCB Retention Yes
PCB Thickness - Recommended 1.60mm
Packaging Type Tube
Pitch - Mating Interface 1.85mm
Pitch - Termination Interface 1.85mm
Plating min - Mating 0.762µm
Plating min - Termination 0.762µm
Polarized to PCB No
Stackable Yes
Surface Mount Compatible (SMC) Yes
Temperature Range - Operating 105°C
Termination Interface: Style Through Hole - Compliant Pin

Electrical

Current - Maximum per Contact 1.0A
Data Rate 8.0 Gbps



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
ED/71/2019 (16 July
2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[75861](#) Series

Mates With

[75676](#) GbX Hybrid Daughtercard. [75671](#)
GbX L-Series Daughtercard

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

GbX 2-Pair by 25- [622022470](#)
Wide L-Series
Insertion Module

Real Signals (per 25mm)	67
Shielded	No
Voltage - Maximum	120V AC (RMS)/DC
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Reference - Drawing Numbers	
Packaging Specification	PK-70873-5058
Sales Drawing	SD-75861-410

This document was generated on 12/17/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[75861-4204](#)