

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0759001441](#)

Status: **Active**

Overview: [MX150™ Unshrouded Header](#)

Description: MX150 Dual Row Header, Right-Angle, 8 Circuits, 1.25µm Nickel (Ni) Overall, 1.50µm Minimum Select Matte Tin (Sn) Plating Overall, 3.05mm PC Tail Length, Mating Pin Length 12.15mm

Documents:

[3D Model](#)

[3D Model \(PDF\)](#)

[Drawing \(PDF\)](#)

[Product Specification PS-75757-000-001 \(PDF\)](#)

[Application Specification AS-75900-204 \(PDF\)](#)

[Packaging Specification PK-36518-351 \(PDF\)](#)

[Packaging Specification PK-75900-0001 \(PDF\)](#)

[Packaging Specification PK-75900-003 \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General


Product Family	PCB Headers
Series	75900
Application	Power, Wire-to-Board
Overview	MX150™ Unshrouded Header
Product Name	MX150
UPC	800756906607

Physical

Breakaway	No
Circuits (Loaded)	8
Circuits (maximum)	8
Color - Resin	Black
Durability (mating cycles max)	25
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	2.937/g
Number of Rows	2
Orientation	Right Angle
PC Tail Length	3.05mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.57mm
Packaging Type	Tube
Pitch - Mating Interface	3.50mm
Pitch - Termination Interface	3.50mm
Plating min - Mating	1.270µm
Polarized to Mating Part	No
Polarized to PCB	No
Shrouded	No
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-40° to +125°C
Termination Interface: Style	Through Hole

Electrical

Current - Maximum per Contact	17.0A
-------------------------------	-------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ECHA_01_2020 (16
January 2020

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[75900 Series](#)

Mates With

[33472 Dual Row MX150 Receptacles](#)

Use With

[33472 MX150 Receptacles Dual Row Housings](#)

Voltage - Maximum 500V DC

Solder Process Data

Duration at Max. Process Temperature (seconds) 005
Lead-free Process Capability WAVE
Max. Cycles at Max. Process Temperature 001
Process Temperature max. C 245

Material Info

Reference - Drawing Numbers

Application Specification AS-75900-204
Packaging Specification PK-36518-351, PK-75900-0001, PK-75900-003
Product Specification PS-75757-000-001
Sales Drawing SD-75900-001-001

This document was generated on 04/01/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[75900-1441](#)