

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0760405010

Status:

Active

Overview:

GbX I-Trac Backplane Connector System

Description:

GbX I-Trac Right-Angle Receptacle Module, 1.85mm by 3.70mm Pitch, Right Guide, 15 Rows, 10 Columns, 300 Circuits

Documents:

3D Model

Packaging Specification PK-70873-608 (PDF)

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Product Specification PS-75710-999-001 (PDF)

Agency Certification

UL

E29179

General

Product Family

Backplane Connectors

Series

76040

Application

Coplanar, Daughtercard

Component Type

PCB Receptacle

Overview

GbX I-Trac Backplane Connector System

Product Name

GbX I-Trac

UPC

822350969390

Physical

Circuits (Loaded)

300

Circuits (maximum)

300

Color - Resin

Black

Durability (mating cycles max)

200

First Mate / Last Break

No

Flammability

94V-0

Guide to Mating Part

Yes

Keying to Mating Part

None

Material - Metal

High Performance Alloy (HPA)

Material - Plating Mating

Gold

Material - Plating Termination

Tin

Material - Resin

High Temperature Thermoplastic

Net Weight

47.794/g

Number of Columns

10

Number of Pairs

8, Open Pin Field

Number of Rows

15

Orientation

Right Angle

PC Tail Length

2.00mm

PCB Locator

Yes

PCB Retention

Yes

PCB Thickness - Recommended

1.60mm

Packaging Type

Tray

Pitch - Mating Interface

1.85mm, 3.70mm

Pitch - Termination Interface

1.00mm, 2.70mm

Plating min - Mating

0.762µm

Plating min - Termination

0.762µm

Polarized to PCB

Yes

Stackable

No

Surface Mount Compatible (SMC)

Yes

Temperature Range - Operating

-55° to +80°C

Termination Interface: Style

Through Hole - Compliant Pin

Electrical



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -

ED/71/2019 (16 July

2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit

Contact US

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

76040 Series

Mates With

76035 GbX I-Trac Vertical Header Module

Use With

78239 GbX I-Trac Right Angle Power Header. 76153 Pirate Cannon Wide Guide Module

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global Description	Product #
Press-In Tool for Right-Angle Receptacle 15-Row, 10-Column	622018624

Current - Maximum per Contact	1.0A	Daughter Card	622023000
Data Rate	12.0 Gbps	Signal Module	
Real Signals (per 25mm)	101	Removal Tool	
Shield Type	N/A		
Shielded	No		
Voltage - Maximum	120V AC (RMS)/DC		
Solder Process Data			
Lead-freeProcess Capability	N/A		
Material Info			
Reference - Drawing Numbers			
Packaging Specification	PK-70873-608		
Product Specification	PS-75710-999-001		
Sales Drawing	SD-76040-004		

This document was generated on 12/17/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[76040-5010](#)