

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0878910101](#)
Status: **Active**
Overview: [KK Interconnect Solutions](#)
Description: KK 254 PCB Header, Through Hole, Vertical, 1 Circuit, Flash Gold (Au) Over 1.27µm Nickel Overall Plating, Tray Packaging, Lead-free

Documents:

3D Model	Packaging Specification PK-89990-934-001 (PDF)
3D Model (PDF)	Test Summary 879200000-TS-000 (PDF)
Drawing (PDF)	Test Summary 879200001-TS-000 (PDF)
Product Specification PS-87920-019-001 (PDF)	RoHS Certificate of Compliance (PDF)
Packaging Specification PK-89990-489-001 (PDF)	

Agency Certification


UL E29179

General

Product Family	PCB Headers
Series	87891
Application	Board-to-Board, Signal, Wire-to-Board
Overview	KK Interconnect Solutions
Product Name	KK 254
UPC	884982606180

Physical

Breakaway	Yes
Circuits (Loaded)	1
Circuits (maximum)	1
Color - Resin	Black
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	None
Mated Height	5.84mm
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Nickel
Material - Resin	Nylon
Net Weight	54.051/mg
Number of Rows	1
Orientation	Vertical
PC Tail Length	2.97mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Packaging Type	Tray
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Plating min - Mating	2.540µm
Plating min - Termination	1.270µm
Polarized to Mating Part	No
Polarized to PCB	No
Shrouded	No
Stackable	No
Temperature Range - Operating	-55° to +105°C



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[87891](#) Series

Mates With

KK PCB Receptacles [4455](#), SL IDT
Housings [70430](#) , 7720, 70400. [90147](#) ,
[90148](#) C-Grid PCB Receptacles

Termination Interface: Style	Through Hole
Electrical	
Current - Maximum per Contact	3.0A
Voltage - Maximum	250V
Solder Process Data	
Duration at Max. Process Temperature (seconds)	012
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	260
Material Info	
Reference - Drawing Numbers	
Packaging Specification	PK-89990-489-001, PK-89990-934-001
Product Specification	PS-87920-019-001
Sales Drawing	SD-87891-001-000, SD-87891-013-001
Test Summary	879200000-TS-000, 879200001-TS-000

This document was generated on 10/04/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[87891-0101](#)