

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0879520003

Status:

Active

Description:

2.54mm Pitch Header, Dual Body, Dual Row, Right-Angle, Through Hole, 6 Circuits (void at circuit 4), 2.54µm Tin (Sn) Overall Plating, Tube Packaging, Lead-Free

Documents:

Drawing (PDF)

Product Specification PS-87920-019-001 (PDF)

Packaging Specification PK-87952-0001-000 (PDF)

Test Summary 879200000-TS-000 (PDF)

Test Summary 879200001-TS-000 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E29179

General

Product Family

Series

Application

Product Name

UPC

PCB Headers

87952

Board-to-Board, Signal, Wire-to-Board

Dual Body

822350179034

Physical

Breakaway

Circuits (Loaded)

Circuits (maximum)

Circuits Detail

Color - Resin

First Mate / Last Break

Flammability

Glow-Wire Capable

Guide to Mating Part

Keying to Mating Part

Lock to Mating Part

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Net Weight

Number of Rows

Orientation

PC Tail Length

PCB Locator

PCB Retention

Packaging Type

Pitch - Mating Interface

Pitch - Termination Interface

Plating min - Mating

Polarized to Mating Part

Polarized to PCB

Shrouded

Stackable

Surface Mount Compatible (SMC)

Temperature Range - Operating

Termination Interface: Style

Yes

6

6

Void at circuit 4

Black

No

94V-0

No

No

No

None

None

Copper Alloy

Tin

Tin

High Temperature Thermoplastic

0.663/g

2

Right Angle

3.46mm

No

None

Tube

2.54mm

2.54mm

2.540µm

Yes

No

No

No

Yes

-55° to +105°C

Through Hole


Electrical

Current - Maximum per Contact

Voltage - Maximum

3.0A

250V



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

87952 Series

Mates With

2.54mm C-Grid & C-Grid III Receptacle, KK Connectors, SL Crimp and IDT Housing

Solder Process Data

Duration at Max. Process Temperature (seconds)	014
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	265

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-87952-0001-000
Product Specification	PS-87920-019-001
Sales Drawing	SD-87952-008-000
Test Summary	879200000-TS-000, 879200001-TS-000

This document was generated on 09/13/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[87952-0003](#)