

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0930704001

Status:


Active

Overview:

RAST Connector System

Description:

Appli-Mate RAST 2.5 Header, Vertical, 11 Circuits, Tin (Sn) Plating, Glow-Wire Capable, Positioning Keys None



Documents:	
3D Model (PDF)	Product Specification PS-99020-0040-001 (PDF)
Drawing (PDF)	Packaging Specification PK-90871-001-001 (PDF)
3D Model	Packaging Specification PK-93070-001-001 (PDF)
Product Specification PS-93070-001-001 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR19980
UL	E29179
Application tooling part link	
Application Tooling Part Link	216658-0100
General	
Product Family	PCB Headers
Series	93070
Application	Power, Wire-to-Board
Comments	""""""""This Molex product is manufactured from material that has the following ratings, tested by independent agencies:. a) A Glow Wire Ignition Temperature (GWIT) of at least 775 deg C per IEC 60695-2-13.. b) A Glow Wire Flammability Index (GWFI) above 850 deg C per IEC 60695-2-12.and hence complies with the requirements set out in the International Standard IEC 60335-1 5th edition - household and similar electrical appliances - safety, section 30 Resistance to heat and fire. <P><P> The customers using this product must determine its suitability for use in their particular application through testing or other acceptable means as described in end-product glow-wire flammability test standard IEC 60695-2-11 and any applicable product end-use standard(s). <P> If it is determined during the customer's evaluation of suitability, that higher performance is required, please contact Molex for possible product options.""""""""
Overview	RAST Connector System
Product Name	RAST 2.5
UPC	883906321260
Physical	
Breakaway	No
Circuits (Loaded)	11
Circuits (maximum)	11
Color - Resin	Natural
Durability (mating cycles max)	10
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	Yes
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

93070 Series

Mates With

Appli-Mate RAST 2.5 Female Connector [93050](#) , Appli-Mate RAST 2.5 IDT Housing [91716](#)

Use With

RAST Standard Interface

Application Tooling FAQ	
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.	
Global	
Description	Product #
RAST 2.5 Power	2166580100
Semi-Automatic IDC	
Machine with R-	
Power Option	

Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Nickel
Material - Resin	Nylon
Net Weight	2.660/g
Number of Rows	1
Orientation	Vertical
PC Tail Length	3.30mm
PCB Locator	Yes
PCB Retention	None
PCB Thickness - Recommended	1.50mm
Packaging Type	Carton
Pitch - Mating Interface	2.50mm
Pitch - Termination Interface	2.50mm
Plating min - Mating	3.048μm
Plating min - Termination	3.048μm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Fully
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-20° to +120°C
Termination Interface: Style	Through Hole
Electrical	
Current - Maximum per Contact	6.0A
Voltage - Maximum	32V
Material Info	
Reference - Drawing Numbers	
Packaging Specification	PK-90871-001-001, PK-93070-001-001
Product Specification	PS-93070-001-001, PS-99020-0040-001
Sales Drawing	930700001-000

This document was generated on 10/04/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93070-4001](#)