

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936011965](#)
Status: **Active**
Overview: [GWconnect® Heavy Duty Connectors \(HDC\)](#)
Description: GWconnect STD-HV - Standard-High Voltage, Single Lever Surface Mount Housing, Die-cast Aluminum, with 1 Lever, with Cover, with Gasket, Size 10B «57x27», Pg21x2 Thread, High Construction, Grey

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification	
CSA	256883
UL	E249674
General	
Product Family	Industrial Connectors / Enclosures
Series	93601
Component Size	10B «57X27»
Component Type	Single Lever SMT Housing
IP Rating	IP66, IP69
Overview	GWconnect® Heavy Duty Connectors (HDC)
Product Category	Heavy Duty Connectors
Product Name	GWconnect
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type	STD-HV
UPC	887191861104
Physical	
Cover Coating	Polyester Powder
Cover Color	Grey RAL 7037
Housing Coating	Polyester Powder
Housing Color	Grey RAL 7037
Lock to Mating Part	Yes
Material - Cover	Die-cast Aluminum
Material - Gasket	NBR
Material - Housing	Die-cast Aluminum
Material - Lever	Galvanized Steel
Mounting Style	Surface Mount
Net Weight	400.000/g
Number of Levers	1
Packaging Type	Bag
Thread Size	Pg21x2
Thread Type	(Pg)
Electrical	
Voltage - Maximum	830V
Material Info	
Engineering Number	7810.7279.2



Series image - Reference only

EU ELV
Not Reviewed

EU RoHS **China RoHS**
Not Reviewed
REACH SVHC
Not Reviewed
Halogen-Free
Status
Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[93601](#) Series

Use With
Size 10B «57x27» , S-EHV Inserts with Screw Terminals and S-HSB Inserts

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-1965](#)