

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0955016669

Status:

Active

Overview:

Magnetic and Modular Jacks/Plugs

Description:

Modular Jack, Right-Angle, Surface Mount, 6/6, Low Profile, Tube

Documents:

3D Model

Application Specification AS-85513-001-001 (PDF)

3D Model (PDF)

Packaging Specification PK-95001-001 (PDF)

Drawing (PDF)

Datasheet (PDF)

Product Specification PS-95501-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E107635

General

Product Family

Modular Jacks/Plugs

Series

95501

Comments

Reflow Capable

Component Type

PCB Jack

Magnetic

No

Overview

Magnetic and Modular Jacks/Plugs

Performance Category

3

Power over Ethernet (PoE)

N/A

Product Name

Modular Jack 6/6

UPC

822350924900

Physical

Boot Color

N/A

Color - Resin

Black

Durability (mating cycles max)

2500

Flammability

94V-0

Inverted / Top Latch

No

Jack Height

11.50mm

Lightpipes/LEDs

None

Material - Metal

Copper Alloy

Material - Plating Mating

Gold over Palladium Nickel

Material - Plating Termination

Tin

Material - Resin

High Temperature Thermoplastic

Net Weight

2.090/g

Orientation

Right Angle (Side Entry)

PCB Locator

Yes

PCB Retention

Yes

PCB Thickness - Recommended

1.57mm

Packaging Type

Tube

Pitch - Mating Interface

1.02mm

Pitch - Termination Interface

1.27mm

Plating min - Mating

0.051µm, 0.600µm

Plating min - Termination

1.905µm

Port Configuration

1x1

Positions / Loaded Contacts

6/6

Surface Mount Compatible (SMC)

Yes

Temperature Range - Operating

-40° to +85°C

Termination Interface: Style

Surface Mount

Waterproof / Dustproof

No

Wire/Cable Type

N/A

Electrical



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -

D(2021)4569-DC (8

July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

95501 Series

Mates With

90075 Modular Plug

Use With

90075

|                               |         |
|-------------------------------|---------|
| Current - Maximum per Contact | 1.5A    |
| Shielded                      | No      |
| Voltage - Maximum             | 125V DC |

**Solder Process Data**

|                                                |        |
|------------------------------------------------|--------|
| Duration at Max. Process Temperature (seconds) | 045    |
| Lead-freeProcess Capability                    | REFLOW |
| Max. Cycles at Max. Process Temperature        | 003    |
| Process Temperature max. C                     | 260    |

**Material Info**

**Reference - Drawing Numbers**

|                           |                  |
|---------------------------|------------------|
| Application Specification | AS-85513-001-001 |
| Packaging Specification   | PK-95001-001     |
| Product Specification     | PS-95501-001     |

This document was generated on 01/03/2022

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[95501-6669](#)