

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0761551803

Status:

Active

Overview:

Impact Backplane Connector and Cable Assembly System

Description:

Impact 100 Ohm 4 Pair Vertical Backplane Header, Unguided, Open Endwall, 8 Columns, 96 Circuits, Pin Length 4.50mm, Plated Through Hole Dimension 0.46mm, Lead-Free

- Documents:
- 3D Model

Application Specification AS-76060-9999-001 (PDF)
- 3D Model (PDF)

Packaging Specification PK-70873-7701-001 (PDF)
- Drawing (PDF)

Test Summary TS-76160-0001-001 (PDF)
- Product Specification PS-76060-999-001 (PDF)

Symbol Footprint Data SYM-76155-1803-001 (PDF)
- Application Specification AS-76060-990-001 (PDF)

RoHS Certificate of Compliance (PDF)
- Application Specification AS-76060-994-001 (PDF)

Agency Certification	
UL	E29179
General	
Product Family	Backplane Connectors
Series	76155
Application	Conventional
Application Tooling Documents	TM-622018799-001
Component Type	PCB Header
Overview	Impact Backplane Connector and Cable Assembly System
Product Name	Impact
UPC	883906417031
Physical	
Circuits (Loaded)	96
Circuits (maximum)	96
Color - Resin	Black
Durability (mating cycles max)	200
First Mate / Last Break	No
Flammability	94V-0
Guide to Mating Part	No
Keying to Mating Part	None
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	2.039/g
Number of Columns	8
Number of Pairs	4
Number of Rows	12
Orientation	Vertical
PC Tail Length	1.40mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.00mm
Packaging Type	Tray
Pitch - Mating Interface	1.90mm
Pitch - Termination Interface	1.90mm
Plating min - Mating	0.762µm
Polarized to PCB	No
Stackable	No



Series image - Reference only

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

76155 Series

Mates With

76160 Impact 100 Ohm Daughtercard

Use With

75234 Backplane Free Standing Guide Pin

Temperature Range - Operating	-55° to +85°C
Termination Interface: Style	Through Hole - Compliant Pin
Electrical	
Current - Maximum per Contact	0.75A
Data Rate	25.0 Gbps
Impedance	100Ω
Shield Type	N/A
Shielded	No
Voltage - Maximum	30V AC (RMS)/DC
Material Info	
Reference - Drawing Numbers	
Application Specification	AS-76060-990-001, AS-76060-994-001, AS-76060-9999-001
Packaging Specification	PK-70873-7701-001
Product Specification	PS-76060-999-001
Sales Drawing	SD-76155-001-001
Symbol/Footprint Data	SYM-76155-1803-001
Test Summary	TS-76160-0001-001

This document was generated on 09/21/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[76155-1803](#)