

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0987881201

Status:

Active

Overview:

NSCC - New Standard Casing Contact

Description:

1.50mm Pitch NSCC, Wire-to-Wire, Receptacle Housing, Gray, 10 Circuits

Documents:

Drawing (PDF)

Application Specification 987880002-AS-CH-001 (PDF)

Application Specification 987880003-AS-CH-001 (PDF)

Application Specification AS-98788-002-001 (PDF)

Application Specification AS-98788-003-001 (PDF)

Application Specification AS-98788-003-FR-001 (PDF)

RoHS Certificate of Compliance (PDF)

Application tooling part link

Application Tooling Part Link	63812-1200
Application Tooling Part Link	63813-5700
Application Tooling Part Link	63813-7400

General

Product Family	Crimp Housings
Series	98788
Application	Power, Wire-to-Wire
Overview	NSCC - New Standard Casing Contact
Product Name	NSCC
UPC	822348791620

Physical

Circuits (maximum)	10
Circuits Detail	10x1.5mm male terminal
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	None
Material - Resin	Polyester
Net Weight	9.590/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	4.25mm
Pitch - Termination Interface	6.00mm
Polarized to Mating Part	Yes
Ports	1
Stackable	No
Temperature Range - Operating	N/A

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Engineering Number	19201EV10M1
--------------------	-------------

Reference - Drawing Numbers

Application Specification	987880002-AS-CH-001, 987880003-AS-CH-001, AS-98788-002-001, AS-98788-003-001, AS-98788-003-FR-001
Sales Drawing	SD-98788-006-001



Series image - Reference only

EU ELV
Compliant

EU RoHS
Compliant
REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free
Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series
98788 Series

Mates With
987891201

Use With
Sicma 1.5 and 2.8mm Female Terminals for
Single Wire Seal from FCI

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Description	Product #
Insertion Tool for Seal Plug	638121200
Extractor Tool for CTX64 Female Crimp Terminals	638135700

This document was generated on 08/27/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[98788-1201](#)