

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0987881208

Status:

Active

Overview:

NSCC - New Standard Casing Contact

Description:

1.50mm Pitch NSCC, Sealed Female Housing, 10 Circuits, Dual Row, White

- Documents:
- Drawing (PDF)

Application Specification 987880002-AS-CH-001 (PDF)

Application Specification 987880003-AS-CH-001 (PDF)

Application Specification AS-98788-002-001 (PDF)

Application Specification AS-98788-003-001 (PDF)

Application Specification AS-98788-003-FR-001 (PDF)

RoHS Certificate of Compliance (PDF)

Application tooling part link

Application Tooling Part Link

63812-1200

Application Tooling Part Link

63813-5700

Application Tooling Part Link

63813-7400

General

Product Family

Crimp Housings

Series

98788

Application

Power, Wire-to-Wire

Overview

NSCC - New Standard Casing Contact

Product Name

NSCC

UPC

822350055512

Physical

Circuits (maximum)

10

Circuits Detail

10x1.5mm male terminal

Color - Resin

Gray

Gender

Receptacle

Glow-Wire Capable

No

Keying to Mating Part

None

Lock to Mating Part

None

Material - Resin

Polyester

Net Weight

9.590/g

Number of Rows

2

Packaging Type

Bag

Panel Mount

No

Pitch - Mating Interface

4.25mm

Pitch - Termination Interface

6.00mm

Polarized to Mating Part

Yes

Ports

1

Stackable

No

Temperature Range - Operating

-40° to +85°C

Solder Process Data

Lead-freeProcess Capability

N/A

Material Info

Engineering Number

19208EV10M8


Reference - Drawing Numbers

Application Specification

987880002-AS-CH-001, 987880003-AS-CH-001, AS-98788-002-001, AS-98788-003-001, AS-98788-003-FR-001

Sales Drawing

SD-98788-006-001



Series image - Reference only

EU ELV
Compliant

EU RoHS
Compliant
REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free
Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Compliant

RoHS Phthalates

Not Contained

Search Parts in this Series
98788 Series

Mates With
987891208

Use With
Sicma 1.5 and 2.8mm Female Terminals for
Single Wire Seal from FCI

Application Tooling | [FAQ](#)
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Insertion Tool for Seal Plug	638121200
Extractor Tool for CTX64 Female Crimp Terminals	638135700

This document was generated on 10/04/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[98788-1208](#)