

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1064152110](#)
Status: **Active**
Overview: [Optical Connectivity Solutions](#)
Description: iPass+ HD-to-iPass+ HD AOC Assembly, Multimode, 50/125µm, 3.00mm CableDiameter, 10.0m Cable Length

Documents:
[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Fiber Optic Assemblies
Series	106415
Boot Type	N/A
Connector to Connector	iPass+ HD-to-iPass+ HD
Mode	Multimode
Overview	Optical Connectivity Solutions
Product Name	AOC, iPass+ HD
UPC	889056484497
Physical	
Cable Length	10.0m
Cable Size	3.00mm
Fiber (Core/Cladding)	50/125µm
Net Weight	158.800/g
Single Ended	No
Wire/Cable Type	Fiber Optic, Round
Material Info	
Reference - Drawing Numbers	
Sales Drawing	1064152105-000



Series image - Reference only

EU ELV Not Relevant	
EU RoHS Compliant with Exemption 7(c)-I REACH SVHC Not Reviewed Halogen-Free Status Not Reviewed	China RoHS
For more information, please visit Contact US	
China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[106415](#) Series

Mates With
iPass+ HD Cage and Receptacle [76866](#) .
iPass+ HD Internal Cable and Connector Assembly [76867](#)

Use With
Mini SAS HD 2.1 4X Cable Assembly [111068](#) , [111077](#) . Internal Cable Assemblies [100190](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

106415-2110