

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1120955071

Status:

Active

Overview:

IP67-Rated HarshIO Modules

Description:

Brad HarshIO Digital Module for Ethernet/IP, Compact 30mm, IP67, 8 ports M8, 8 User conf. Inputs/Outputs, PNP, M12 5-Pole Power



Documents:

[Drawing \(PDF\)](#)

[Product Literature \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Industrial I/O Modules
Series	112095
Application	Filling and Packaging Machines, Machine Tool Industry, Material Handling Systems
Approvals	ODVA, UL, cUL, CE
Comments	Universal and user configurable input / output channels., Universal and user configurable input / output channels.
EPLAN	Yes
IP Rating	IP67
Overview	IP67-Rated HarshIO Modules
Product Name	HarshIO EtherNet/IP
Protocol	EtherNet/IP
Software Downloads	TBDEI-xYYP-D8x
UPC	887191132051
Physical	
Bus Input	4-pole Micro-Change (M12), D-Coded, Female
Bus Output	4-pole Micro-Change (M12), D-Coded, Female
Format	Compact (30mm)
Housing Width	30.00mm
I/O Connector	5-pole Ultra-Lock (M12), A-Coded, Female
I/O Ports	8x M8
I/O Signal Mix	8 input / output configurable
Mechanical Shock	10G, 11ms, 3 AXIS
Net Weight	200.000/g
Power Input	5-pole Micro-Change (M12), A-Coded, Male
Power Output	None
Temperature Range - Operating	-25°C to +70°C
Vibration	MIL-STD-202F, Test Method 204D,Condition A
Electrical	
Current - Maximum Output	0.5A per Channel
EMC	IEC 61000-6-2
Input Delay	0.5 to 3ms
Input Device Supply	250 mA per port at 25°C
Input Type	PNP or Dry Contact
Material Info	
Engineering Number	TBDEI-8YYP-D84
Reference - Drawing Numbers	
Sales Drawing	1120955064-000

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit

Contact US

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

112095 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

112095-5071