

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1200062799

Status:


Active

Overview:

Brad Micro-Change (M12) Connectors

Description:

Micro-Change (M12) Single-Ended Cordset, 5 Poles, Male (Straight) to Pigtail, 0.34mm² PVC Cable, 1.0m (3.28') Length



Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E152210

General

Product Family

Industrial Cordsets

Series

120006

Connector End A

Micro-Change (M12)

Connector End B

Pigtail

IP Rating

IP67

Material - Contact

Copper Alloy

Overview

Brad Micro-Change (M12) Connectors

Product Name

Micro-Change (M12)

Protocol

N/A

Region

Europe

Type

Single Ended

UPC

883906138394

Physical

Cable Diameter

5.80mm (.230")

Cable Length

1.0m (3.28')

Color - Cable Jacket

Black

Coupling Style

Threaded

Gender

Male-Pigtail

Keyway

Single

LED Indicator

No

Material - Cable Jacket

PVC

Material - Connector Body

PUR

Material - Coupling Nut

Nickel-plated Brass

Material - O-Ring

Fluoro-elastomer

Material - Plating Mating

Gold

Net Weight

50.000/g

Orientation

Straight to Pigtail

Poles

5

Temperature Range - Operating

-30° TO +80°C

Wire Size AWG

N/A

Wire/Cable Type

UL 2464

Electrical

Current - Maximum per Contact

4.0A

Voltage - Maximum

250V AC/DC

Material Info

Engineering Number

805006E03M010

Reference - Drawing Numbers

Sales Drawing

1200659185-000

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - D(2021)4569-DC (8 July 2021)

Lead

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

ZZCERT_CE -

CER_4000380980_00_000.pdf

Declaration of

Conformity

Search Parts in this Series

120006 Series

This document was generated on 01/03/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1200062799