

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1200652265

Status:

Active

Overview:

Brad Micro-Change (M12) Connectors

Description:

Micro-Change (M12) Single-Ended Cordset with Knurled Hexnut, 4 Poles, Female (90°) to Pigtail, 22 AWG, Black TPU WSOR Cable, 5.0m (16.40') Length

Documents:	
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E152210
General	
Product Family	Industrial Cordsets
Series	120065
Connector End A	Micro-Change (M12)
Connector End B	Pigtail
IP Rating	IP67
Material - Contact	Brass
Overview	Brad Micro-Change (M12) Connectors
Product Name	Micro-Change (M12)
Protocol	N/A
Region	Europe
Type	Single Ended
UPC	887191554792
Physical	
Cable Diameter	5.10mm (.201")
Cable Length	5.0m (16.40')
Color - Cable Jacket	Black
Coupling Style	Knurled Hexnut, Threaded
Gender	Female-Pigtail
Keyway	Single
LED Indicator	No
Material - Cable Jacket	TPU
Material - Connector Body	TPU
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Net Weight	217.500/g
Orientation	90° to Pigtail
Poles	4
Temperature Range - Operating	-25° to +85°C
Wire Size AWG	22
Wire/Cable Type	UL 21215
Electrical	
Current - Maximum per Contact	4.0A
Voltage - Maximum	60V
Material Info	
Engineering Number	804001B30M050
Reference - Drawing Numbers	
Sales Drawing	SD-120065-076-001



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant with Exemption 6(c)	
REACH SVHC	
Contained Per - D(2021)4569-DC (8 July 2021)	
Lead	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained
ZZCERT_CE - Declaration of Conformity	CER_4000380967_00_000.pdf

Search Parts in this Series

120065 Series

This document was generated on 01/17/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1200652265