

PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION

**Part Number:** [1200895003](#)  
**Status:** **Active**  
**Overview:** [Brad Nano-Change \(M8\) Products](#)  
**Description:** Y Nano-Change (M8) Splitter to Nano-Change (M8) 4 Pole Female to 4 Pole Male

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family Industrial Tees and Splitters  
Series [120089](#)  
IP Rating IP67  
Overview [Brad Nano-Change \(M8\) Products](#)  
Product Name Nano-Change (M8)  
Type Splitter - Solid Body  
UPC 883906319472

**Physical**

Drop Connector Nano-Change (M8)  
Drop Gender Male  
Keyway None  
Left Trunk Connector Nano-Change (M8)  
Left Trunk Gender Female  
Leg 1 Length N/A  
Leg 2 Length N/A  
Material - Cable Jacket N/A  
Material - Connector Body PUR  
Material - Coupling Nut Nickel-plated Brass  
Net Weight 1.000/g  
Poles 3  
Right Trunk Connector Nano-Change (M8)  
Right Trunk Gender Female  
Temperature Range - Operating -20°C to +90°C

**Electrical**

Current - Maximum per Contact 4.0A  
Voltage - Maximum 60V AC / 75V DC

**Material Info**

Engineering Number 0808 04LMF 00001

**Reference - Drawing Numbers**

Sales Drawing SD-120089-002

**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

50 Image

Not Relevant

Not Reviewed

**Search Parts in this Series**

[120089](#) Series

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1200895003