

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1300280048

Status:

Active

Overview:

DeviceNet Solutions

Description:

Micro-Change (M12) Double-Ended Cordset, 5 Poles, Male (Straight) to Female (Straight), 22 AWG, DeviceNet Thin Stranded Cable, 15.0m (49.21') Length



Series image - Reference only

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR6837
UL	E152210
General	
Product Family	Industrial Cordsets
Series	130028
Connector End A	Micro-Change (M12)
Connector End B	Micro-Change (M12)
IP Rating	IP67
Material - Contact	Copper Alloy
Overview	DeviceNet Solutions
Product Name	DeviceNet, Micro-Change (M12)
Protocol	N/A
Region	Europe
Type	Double Ended
UPC	78678849594
Physical	
Cable Diameter	7.24mm (.285")
Cable Length	15.0m (49.21')
Color - Cable Jacket	Gray
Coupling Style	Threaded
Gender	Female-Male
Keyway	Single
LED Indicator	No
Material - Cable Jacket	PVC
Material - Connector Body	PVC
Material - Coupling Nut	Die-Cast Zinc
Material - Plating Mating	Gold
Net Weight	355.600/g
Orientation	Straight to Straight
Poles	5
Temperature Range - Operating	-20° to +80°C
Wire Size AWG	22
Wire/Cable Type	Shielded-Twisted Pair
Electrical	
Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC/DC
Material Info	
Engineering Number	DND22A-M150
Reference - Drawing Numbers	
Sales Drawing	SD-130028-001-001

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

130028 Series

This document was generated on 01/17/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1300280048