






13	12	11	10
MATERIAL NO.	ENGINEERING NO.	STD MATERIAL	UV MATERIAL
1300550014	ENSP6F5	1A	
1300550015	ENSP6F5-V		1B



PANEL CUT OUT  
 PANEL THK: .125 MAX. W/GASKET  
 .187 MAX. W/OUT GASKET  
 .062 MIN.



- NOTES:  
 1. MATERIAL: SEE TABLE  
 2. FINISHES: SEE TABLE  
 3. ELECTRICAL SPEC: VOLTAGE: 125 VDC, CURRENT: 1.5 AMPS  
 4. OPERATING TEMP: -20 TO 80°C (-4 TO 176°F)  
 5. ENVIRONMENTAL: IP67

5	PANEL NUT	ABS	BLACK
4	RJ-11/PCB SUB ASSEMBLY		
3	BULKHEAD GASKET	NITRILE	BLACK
2	O-RING	VITON	BROWN
1B	RECEPTACLE HOUSING (UV)	ASA	BLACK
1A	RECEPTACLE HOUSING	ABS	BLACK
ITEM	DESCRIPTION	MATERIAL	FINISH

CORRECT THREAD DIM EC NO: IPG2017-0838 DRWN:MZIELINSKI 2017/03/03 CHK:DRSTONE 2017/03/06 APPR:WOODMAN 2017/03/13 B1	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 2:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION			
				mm	INCH	DRAWN BY	DATE	TITLE INDUSTRIAL ETHERNET RJ-11 BULKHEAD FEED THRU				
			4 PLACES	± ---	± ---	RSTONE	2010/06/24					
			3 PLACES	± ---	± ---	CHECKED BY	DATE	MOLEX INCORPORATED				
			2 PLACES	± ---	± ---	B. WOODMAN	2010/06/25					
			1 PLACE	± ---	± ---	APPROVED BY	DATE	SD-130055-001				
			ANGULAR ± ---°		DTITUS	2010/06/28						
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO.		DOCUMENT NO.		SHEET NO.			
					SEE CHART				1 OF 1			
					SIZE C		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1300550015