


13	12	11	10	9	8	7	6	5	4	3	2	1
POLES	MATERIAL NO.	ENG. NO.	AMPS	LENGTH								
3	1300640065	CC3030A48M020	32	2M +89-0MM (6'7"+3.50-0)								
4	1300640187	CC4030A48M020	32	2M +89-0MM (6'7"+3.50-0)								
4	1300640245	CC4030A48M100	32	10M +318-0MM (32'10" +12.5"-0")								



SPECs: OVERMOLD: GRAY PVC INSERT: BLACK PVC COUPLING NUT: ANODIZED ALUMINUM CABLE: #10AWG GRAY PVC DUAL RATED UL TC/OPEN WIRING & ST00W ELECTRICAL: 600V AC/DC		ADDED PART NUMBER EC NO: IPG2016-1155 DRWNGGUSTAFSON 2016/02/23 CHKDHZIELINSKI 2016/03/15 APPR:BMWOODMAN 2016/02/23		QUALITY SYMBOLS ▽=0 ▽=0		GENERAL TOLERANCES (UNLESS SPECIFIED)<table><tr><th></th><th>mm</th><th>INCH</th></tr><tr><td>4 PLACES</td><td>± .---</td><td>± .---</td></tr><tr><td>3 PLACES</td><td>± .---</td><td>± .005</td></tr><tr><td>2 PLACES</td><td>± .---</td><td>± .010</td></tr><tr><td>1 PLACE</td><td>± .---</td><td>± .020</td></tr></table>ANGULAR ±1/2°			mm	INCH	4 PLACES	± .---	± .---	3 PLACES	± .---	± .005	2 PLACES	± .---	± .010	1 PLACE	± .---	± .020	DIMENSION STYLE IN/MM DRAWN BY DATE B.RUPERT 01/12/10 CHECKED BY DATE B.WOODMAN 01/12/10 APPROVED BY DATE JFMURPHY 2010/01/15		SCALE 1:2		DESIGN UNITS INCH		THIRD ANGLE PROJECTION	
	mm	INCH																												
4 PLACES	± .---	± .---																												
3 PLACES	± .---	± .005																												
2 PLACES	± .---	± .010																												
1 PLACE	± .---	± .020																												
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		MOLEX INCORPORATED		QUICK CHANGE FEMALE/MALE STRAIGHT 3 & 4 POLE AS PORTABLES		SHEET NO. 1 OF 1																		
								THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																						

1b_frame_C_P_AM_T Rev. E 2006/04/15	12	11	10	9	8	7	6	5	4	3	2	1
--	----	----	----	---	---	---	---	---	---	---	---	---

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1300640077