

F

E

D

C

B

A

F

E

D

C

B

A


22/4 AWG ITC/PLTC YELLOW TPE CABLE
GENERAL SPECIFICATIONS

PHYSICAL CHARACTERISTICS:

CONDUCTOR PAIR SIZE	#22 (19 x #34) BARE COPPER
INSULATION TYPE	PVC INSULATION
COLORS	BLACK, BROWN, BLUE, WHITE
OUTSIDE DIAMETER	ø.205" REF.
JACKET MATERIAL	TPE YELLOW

ENVIRONMENTAL CHARACTERISTICS:

FLAME RESISTANCE	FT4 APPROVED
AGENCY CERTIFICATIONS	UL ITC E195601 OR PLTC CSA AWM I/II A/B, FT4 LL54185 ALTERNATIVE CSA-US ITC LL54185-02 OR PLTC CSA AWM I/II A/B, FT4
OPERATING TEMPERATURE	-40°C TO 105°C
OIL RESISTANCE	OIL RES II
ENVIRONMENTAL	SUNLIGHT RESISTANT



COLOR ROTATION

MECHANICAL CHARACTERISTICS:

TORSIONAL FLEX TEST	10 MILLION CYCLES PER MIL-C-13777G
BEND FLEX TEST	10 MILLION CYCLES PER MIL-C-13777G
WELD SLAG RESISTANCE	WOODHEAD STANDARD S-300

ADDED SUNLIGHT RESISTANT NOTE EC NO: IPG2016-1251 DRWN: GGUSTAFS 2016/03/11 CHKD: MZIELINS 2016/04/07 APPR: BWOODMAN2016/03/04	DESCRIPTION REV	QUALITY SYMBOLS <div>▽=0</div> <div>▽C=0</div>	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE INCH		SCALE NTS	DESIGN UNITS INCH	THIRD ANGLE PROJECTION <div>⊙</div> <div>□</div>					
				mm	INCH	DRAWN BY GGUSTAFS	DATE 2016/02/23	TITLE 22AWG YLW TPE CBL ITC/PLTC - 105Â°C - 330V 4 CONDUCTOR - FT4							
			4 PLACES	±---	±---	CHECKED BY RSTONE	DATE 2016/03/16								
			3 PLACES	±---	±.005	APPROVED BY BWOODMAN		MATERIAL NO. 1302100079	DOCUMENT NO. SD-130210-005	SHEET NO. 1 OF 1					
			2 PLACES	±---	±.010										
			1 PLACE			±---	±.020								
			ANGULAR ±.5°												
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS												
</															

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1302100079