

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION


Part Number: [1501792100](#)
Status: **Active**
Overview: [Standard .062"+ and Standard .062" Pin and Socket Connector Systems](#)
Description: [Standard .062"+ Receptacle Housing, Dual Row, 10 Circuits](#)

Documents:
[3D Model](#) [Packaging Specification PK-150176-001-001 \(PDF\)](#)
[3D Model \(PDF\)](#) [Test Summary 1501760001-TS-000 \(PDF\)](#)
[Drawing \(PDF\)](#) [Datasheet \(PDF\)](#)
[Product Specification 1501760001-PS-000 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Application Specification 1501760001-AS-000 \(PDF\)](#)

Agency Certification	
UL	E29179
General	
Product Family	Crimp Housings
Series	150179
Application	Power, Wire-to-Wire
Overview	Standard .062"+ and Standard .062" Pin and Socket Connector Systems
Product Name	Standard .062"+
UPC	889056490306
Physical	
Circuits (maximum)	10
Color - Resin	Natural
Flammability	94V-2
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	2.459/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	N/A
Pitch - Mating Interface	3.68mm
Pitch - Termination Interface	3.68mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C

Material Info

Reference - Drawing Numbers	
Application Specification	1501760001-AS-000
Packaging Specification	PK-150176-001-001
Product Specification	1501760001-PS-000
Sales Drawing	SD-150179-001-000
Test Summary	1501760001-TS-000



Series image - Reference only

EU ELV
Compliant

EU RoHS **China RoHS**
Compliant
REACH SVHC
Not Contained Per -
D(2020)9139-DC (19
Jan 2021)
Halogen-Free
Status
Low-Halogen
For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series
[150179](#) Series

Mates With
Standard .062"+ Plug Housing [150177](#)

Use With
Standard .062"+ Female Terminal [150181](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[150179-2100](#)