

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0787261004

Status:

Active

Overview:

DDR4 DIMM Sockets

Description:

DDR4 DIMM Socket, Vertical Through-Hole, 0.76µm Gold Plating, 288 Circuits, PCB Thickness 1.57mm, Tail Length 2.67mm, Black Housing, White Latch

Documents:

3D Model (PDF)

3D Model


Drawing (PDF)

Product Specification PS-78726-001-001 (PDF)

Application Specification AS-78726-002-001 (PDF)

Packaging Specification PK-78726-001-000 (PDF)

RoHS Certificate of Compliance (PDF)



Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	Memory Module Sockets
Series	78726
Component Type	Socket
JEDEC Outline	MO-309
Overview	DDR4 DIMM Sockets
Product Name	DDR4 DIMM
UPC	887191398853
Physical	
Circuits (Loaded)	288
Circuits (maximum)	288
Durability (mating cycles max)	25
Entry Angle	Vertical (Top Entry)
Flammability	94V-0
Housing Color	Black
Keying to Mating Part	None
Latch Color	White
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	6.626/g
PC Tail Length	2.67mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.57mm
Packaging Type	Tray
Pitch - Mating Interface	0.85mm
Pitch - Termination Interface	0.85mm
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Temperature Range - Operating	-55° to +85°C
Termination Interface: Style	Through Hole
Electrical	
Current - Maximum per Contact	0.75A
Voltage - Maximum	29V AC (RMS)/DC
Solder Process Data	
Duration at Max. Process Temperature (seconds)	005
Lead-freeProcess Capability	SMC&WAVE

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

78726 Series

Max. Cycles at Max. Process Temperature	002
Process Temperature max. C	260

Material Info

Reference - Drawing Numbers

Application Specification	AS-78726-002-001
Electrical Model Document	787260005-000, EE-78726-002-001, EE-78726-004-001
Packaging Specification	PK-78726-001-000
Product Specification	PS-78726-001-001
S-Parameter Model	787260005-000, SP-78726-002-001, SP-78726-004-001
Sales Drawing	SD-78726-002-000

This document was generated on 10/04/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

78726-1004