


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1511195026](#)
Status: **Active**
Overview: [Milli-Grid Connector System](#)
Description: 2.00mm Pitch, Milli-Grid PCB Header, Dual Row, Right-Angle, Through Hole, 2.00µm Tin (Sn) Plating, without Peg, 4.60mm PC Tail Length, without Pick and Place Tape, 26 Circuits, Glow-Wire Capable, Tube



Documents:	
3D Model	Application Specification 503940002-AS-000 (PDF)
3D Model (PDF)	Packaging Specification PK-151119-0001-001 (PDF)
Drawing (PDF)	Packaging Specification PK-151119-3000-001 (PDF)
Product Specification PS-151117-0001-001 (PDF)	Datasheet (PDF)
Application Specification 503940001-AS-000 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	PCB Headers
Series	151119
Application	Board-to-Board, Signal, Wire-to-Board
Overview	Milli-Grid Connector System
Product Name	Milli-Grid
UPC	889056751667

Physical	
Breakaway	No
Circuits (Loaded)	26
Circuits (maximum)	26
Color - Resin	Black
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	Yes
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Liquid Crystal Polymer
Net Weight	1.497/g
Number of Rows	2
Orientation	Right Angle
PC Tail Length	4.60mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	3.60mm
Packaging Type	Tube
Pitch - Mating Interface	2.00mm
Pitch - Termination Interface	2.00mm
Plating min - Mating	2.000µm
Plating min - Termination	2.000µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Yes
Stackable	No

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[151119](#) Series

Mates With
Milli-Grid Receptacle Housing [151192](#) ,
[51110](#)
Milli-Grid PCB Receptacles
[78787](#) , [78788](#) , [79107](#) , [79109](#)

Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-55° to +105°C
Termination Interface: Style	Through Hole

Electrical

Current - Maximum per Contact	2.0A
Voltage - Maximum	125V AC

Solder Process Data

Duration at Max. Process Temperature (seconds)	010
Lead-freeProcess Capability	SMC&WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	260

Material Info

Reference - Drawing Numbers

Application Specification	503940001-AS-000, 503940002-AS-000
Packaging Specification	PK-151119-0001-001, PK-151119-3000-001
Product Specification	PS-151117-0001-001
Sales Drawing	SD-151119-0001-001

This document was generated on 09/06/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[151119-5026](#)