

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0850032737

Status:


Active

Overview:

DIN 41612

Description:

2.54mm Pitch DIN 41612 C/2 Style Male Header, Right-Angle, Through Hole, 0.80µm Selective Gold (Au) Plating, 48 Circuits, without Mounting Clips, No Flux Proof, Lead-Free



Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	Backplane Connectors
Series	85003
Application	Backplane
Comments	No Mounting Clips. No Flux Proof. 4.20mm Last-Mate-First-Break Contacts. 5.40mm First-Mate-Last-Break Contacts. 4.80mm Normal Contacts, No Mounting Clips. No Flux Proof. 4.20mm Last-Mate-First-Break Contacts. 5.40mm First-Mate-Last-Break Contacts. 4.80mm Normal Contacts
Component Type	PCB Header
Overview	DIN 41612
Product Name	IEC 603-2/DIN 41612
Style	C/2
UPC	800753873957
Physical	
Circuits (Loaded)	48
Circuits (maximum)	48
Circuits Detail	Standard Contacts at: A:a1-a14,a16; B:b1,b3-b14,b16; C:c1-c10,c12-c14,c16. First-Mate-Last-Break Contacts at: X:c11,c15; Y:b2,b15; Z:a15
Color - Resin	Gray
Durability (mating cycles max)	400
First Mate / Last Break	Yes
Flammability	94V-0
Guide to Mating Part	No
Keying to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Polyester
Net Weight	7.363/g
Number of Columns	16
Number of Pairs	Open Pin Field
Number of Rows	3
Orientation	Right Angle
PC Tail Length	3.00mm
PCB Locator	No
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Carton
Pitch - Mating Interface	2.54mm

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/71/2019 (16 July 2019)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

85003 Series

Pitch - Termination Interface	2.54mm
Plating min - Mating	0.813μm
Plating min - Termination	2.540μm
Polarized to PCB	Yes
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-55° to +125°C
Termination Interface: Style	Through Hole
Electrical	
Current - Maximum per Contact	1.0A
Data Rate	622.0 Mbps
Voltage - Maximum	250V AC (RMS)
Solder Process Data	
Duration at Max. Process Temperature (seconds)	010
Lead-freeProcess Capability	WAVE
Process Temperature max. C	260
Material Info	
Reference - Drawing Numbers	
Sales Drawing	SD-85003-2737

This document was generated on 09/17/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[85003-2737](#)