

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0850091110

Status:


Active

Overview:

DIN 41612

Description:

2.54mm Pitch DIN 41612 M Style Male Header, Right-Angle, Through Hole, 28 Circuits, with Mounting Clips, No Flux Proof



Documents:	
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	Backplane Connectors
Series	85009
Application	Backplane
Comments	With Mounting Clips. No Flux Proof, With Mounting Clips. No Flux Proof
Component Type	PCB Header
Overview	DIN 41612
Product Name	IEC 603-2/DIN 41612
Style	M
UPC	800753286986
Physical	
Circuits (Loaded)	28
Circuits (maximum)	42
Circuits Detail	Standard Contacts at: A:a10-a23, C:c10-c23
Durability (mating cycles max)	400
First Mate / Last Break	No
Flammability	94V-0
Guide to Mating Part	No
Keying to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Number of Columns	14
Number of Pairs	Open Pin Field
Number of Rows	3
Orientation	Right Angle
PC Tail Length	3.00mm
PCB Locator	No
PCB Retention	Yes
Packaging Type	Tray
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Plating min - Mating	0.610µm
Plating min - Termination	2.540µm
Polarized to PCB	Yes
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-55° to +125°C
Termination Interface: Style	Through Hole
Electrical	
Current - Maximum per Contact	1.0A

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit

Contact US

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

85009 Series

Data Rate	622.0 Mbps
Voltage - Maximum	250V AC (RMS)

Material Info

Reference - Drawing Numbers
Sales Drawing

SDA-85009-0002, SDA-85009-1110

This document was generated on 09/14/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

85009-1110