


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0850840700](#)
Status: **Active**
Overview: SRC - Sealed Rectangular Connectors
Description: SRC Housing, Female, Hybrid 66 Pin Mixed Power and Signal (60 x MX150 + 6 x MX150L), SPS/Nylon, Black



Documents:
[Drawing \(PDF\)](#)
[Product Specification 850700010-K \(PDF\)](#)
[Product Specification 937320001-P \(PDF\)](#)
[Application Specification 850830010-A \(PDF\)](#)
[Packaging Specification 937320001-K \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)
[Product Literature \(PDF\)](#)

General
Product Family Crimp Housings
Series [85084](#)
Application Power, Signal, Wire-to-Wire
Overview [SRC - Sealed Rectangular Connectors](#)
Product Literature Order No 987650-7391
Product Name SRC
UPC 883906945572

Physical
Circuits (maximum) 66
Circuits Detail 60 x MX150™ + 6 x MX150L™
Color - Resin Black
Gender Receptacle
Glow-Wire Capable No
Keying to Mating Part None
Lock to Mating Part Yes
Material - Resin SPS/Nylon
Net Weight 106.910/g
Number of Rows 12
Packaging Type Tray
Panel Mount No
Pitch - Mating Interface 0.30mm
Polarized to Mating Part Yes
Stackable No
Temperature Range - Operating -40° to +125°C

Material Info

Reference - Drawing Numbers
[Application Specification 850830010-A](#)
[Packaging Specification 937320001-K](#)
[Product Specification 850700010-K, 937320001-P](#)
[Sales Drawing 850840700-000](#)

EU ELV
Not Relevant

EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - ED/71/2019 (16 July 2019)	
Halogen-Free Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[85084 Series](#)

Mates With
SRC Power Blade Housing [850830300](#) , [937926006](#)

Use With
MX150 Female Terminals [33012](#) . MX150L Female Terminal [19434](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

85084-0700